



## Ordering guide

Example: HFP1120 P4 A N PM

Product Code	Post Diameter	Finish	Arm Accessory	Post Matching
<b>HFP1120</b>				<b>PM</b>
<b>HFP1120</b> Twin	<b>P4</b> 4" Post Mount <b>P5</b> 5" Post Mount <b>P6</b> 6" Post Mount	<b>A</b> Black <b>B</b> White <b>G</b> Verde <b>H</b> Bronze <b>J</b> Green	<b>N</b> None <b>F</b> Finial <b>R</b> Twistlock receptacle	<b>PM</b> Post Matching

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Specifications

### Housing

6063-T6 Extruded aluminum.

### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Warranty

Three-year limited warranty.

Height	Length	EPA
61" (155 cm)	100" (254 cm)	4.06 sq. ft

