



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets						
	Open Downlight					Adjustable	Enclosed
	Aperture Cone	Satin Cone	Baffles	Slot	Pinhole	Mini Swivel	Diffuser
2000LVNT	<b>2012</b> <b>2012NM</b> <b>2013BKNM</b> <b>2013CD</b> <b>2013CDNM</b> <b>2013NM</b> <b>2013BK</b> <b>2013WH</b> <b>2013</b> <b>2013WD</b> <b>2013WDP</b>	<b>2008</b> <b>2008NM</b> <b>2010</b> <b>2010NM</b>	<b>2005</b> <b>2005WH</b> <b>2005BNM</b> <b>2005NM</b>	<b>2006</b>	<b>2011</b>	<b>2025WH</b>	<b>2090LV</b> <b>2026WH</b>

### Features

- Mounting Frame:** 0.036" galvanized steel. Accommodates all ceilings up to 1" thick. (Push-in/twist-out rotoclips hold reflector flush to ceiling.)
- Junction Box:** 4" x 3 1/2" x 2"; 0.063" galvanized steel. U.L. listed for; maximum of 8 No. 12 ga. 90° C through branch circuit supply conductors (75° C end of run). Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** 0.059" galvanized steel 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- Socket Housing:** Aluminum, with lamp adjustment assembly allows 35° max. vertical, 358° horizontal adjustment.
- Socket:** Field replaceable. Two pin socket, pre-wired with #18 SF1 leads to junction box.
- Transformer:** Frame-in Kit is provided without transformer. Transformer must be provided by others. Lightolier Cat. #8608 or 8609 transformers may be used. Frame-in Kit is rated at 50VA. Use only 12V. A.C. input.
- Thermal Protector:** Meets NEC and UL requirements. Insulation must be kept 3" away from fixture sides and wiring compartments and must not be placed above fixture in a manner which will entrap heat.

# 2000LVNT Lytecaster Low Voltage 3 3/4"

## MR16 Remote Transformer

### Dimming

**Dimming Controls:** Use only dimmers specifically designed for use with transformers, like Lightolier Onset®, Sunrise® series LV or VA dimmers, or any Lightolier Controls dimming system. Low voltage fixtures may produce audible sound when used with dimmers, which may be objectionable in acoustically critical areas.

### Options and Accessories

<b>Mounting Bars:</b>	<b>1964</b> - 20" set of (2)
<b>T-Bar Ceiling Clips:</b>	<b>1956</b> - set of (4)
<b>Plaster Ceiling Ring:</b>	<b>1959</b> - 7/8" deep for wet plaster ceilings.
<b>MR16 Socket Replacement:</b>	<b>1975B</b>
<b>Remote Transformer:</b>	<b>8608</b> or <b>8609</b>

### Labels

UL (Suitable for Damp Locations), I.B.E.W.

Romex® is a registered trademark of General Cable Industries Inc.

