

Day-Brite

CFI

by  Signify

Linear

VTC Sealed strip



Rugged reliability for efficient environments

The Day-Brite/CFI LED Sealed strip will work hard and long to give you the durability you are looking for in challenging locations.

This luminaire was designed for peace of mind. The Sealed strip is a superb choice for tough environments both indoor and out.

- More than 40% energy savings compared to 2x 32T8
- Reliable LED technology, ensuring maintenance free long life
- Direct replacement for conventional vapor tight luminaire

Choose lighting you can count on for you and your customers.



VTC Sealed strip

Linear LED



Job ready and durable.

- Grey one piece, molded polycarbonate body. No rusting, no oxidation, and no corrosion.
- Standard lens is frosted.
- Gasket provides tight seal between plastic lens and housing.
- Stainless steel latches are standard.
- Hanging V hooks included (set of 2).
- Wrap around mounting brackets included (set of 2).
- cULus listed to meet UL 1598 standards for -10C to 40C ambient. Suitable for wet locations.
- 5 Year Limited Warranty


Ordering guide

Example: VTC436L840-UNV

Series	Length (nominal)	Lumens' (nominal)	Color temp. (K)	Voltage
VTC	4	36L	840 -	UNV
VTC Sealed strip LED	4 4' length	36L 3600 lumens	840 80 CRI, 4000K	UNV Universal voltage 120-277V (non-dimmable)

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.

Dimensions



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

