



Lightolier **Mini Gimbal** Downlight provides an easy to install adjustable three-inch solution for accent lighting. The small detachable junction box eliminates the need for a traditional frame in or bulky remodeler kit making installation quick and easy.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Fixture

example: MG3R06930NF1W

Family	Size	Lumens	CRI	CCT	Beam Spread	Voltage	Finish
MG	3R	06	9		NF	1	
MG Mini Gimbal	3R 3-inch Round	06 550 lm	9 90CRI	30 3000K 40 4000K	NF Narrow Flood	1 120V	W White B Black N Brushed Nickel

Accessories

example: MDRN

Family	Model
MD	
MD Mini Downlight / Gimbal	RN Round new construction plate 06C 6' extension cable 20C 20' extension cable

Specifications

Features

- Flange:** Die cast aluminum. white painted.
- Junction box:** Steel. Clip attached on the side of the junction box to connect with fixture or new construction plate to meet NEC (National Electric Code). Also has key holes on the sides for mounting on joist.
- Connector:** Locking power connection is used to connect junction box and fixture. Standard length of the connector is 6". Extension cables are available as accessory.
- Ceiling cutout:** installation template and ceiling cutout template is supplied with the product. 2 3/4" (70mm) diameter.
- Lifetime:** L₇₀ at 50,000 hours and backed by a 5-year warranty (see signify.com/warranties for details).
- Compliance:** New Construction plate. Steel. Holes on the side of the plate for mounting.
- Adjustability:** 30° tilt and 360° rotation

Electrical

Electronic power supply: RoHS compliant. Class 2 power unit. Remote power supply can only accommodate one LED module and cannot be shared with other LED module.

Fixture can be daisy chained and cannot be through wired.

Dimming: Intended for TRIAC dimming. For more details, please see LED-DIM-DL spec sheet.

Listings



cETLus listed.
Ceiling-mounted: suitable for damp location.
ENERGY STAR®.
Title 24 (JA8-2016).
IC rated.
AirSeal for minimal air leakage.

MG Mini Gimbal LED 3" round


Downlighting

Dimensions


Fixture



Junction box




New Construction Plate



Components

1. Electrical box with knockouts
2. Mounting keyhole
3. NEC* mounting clip
4. 6" (0.15) cord each side. 12" over
5. Lockin power connector
6. Integrated LED Luminaire
7. Spring clip for easy mounting





MG Mini Gimbal LED 3" round

Downlighting

Aiming angles


L and W are the outer points where the candle power drops to 50% of the maximum. FC are the initial footcandles at the center of the beam. Data shown is for 3000K, use the table on the right for CRI/CCT adjustment factors.

L Beam length
D Distance
W Beam Width
A Aiming Angle
FC Footcandles
C Distance to center beam
CBCP Center Beam Candlepower.



3000K, 8W, 74 lm/W

Candela Curve



Fixture: MG3R06930NF1W

Output lumens: 592 lm
Input watts: 8.0 W
CRI: 90 min
CCT¹: 3000K
Center Beam.: 2340cd
Beam Angle: 23°

Efficacy: 74.0 lm/w

30° Horizontal Aiming


Distance		F.C.	Beam	
D	C		L	W
6	3.5	42	3.3	2.8
8	4.6	24	4.4	3.8
10	5.8	15	5.5	4.7
12	6.9	11	6.6	5.6

30° Vertical Aiming

Distance		F.C.	Beam	
D	C		L	W
2	3.5	73	3.7	1.6
3	5.2	33	5.6	2.4
4	6.9	18	7.4	3.3
5	8.7	12	9.3	4.1

4000K, 8W, 80 lm/W

Candela Curve



Fixture: MG3R06940NF1W

Output lumens: 650 lm
Input watts: 8.1 W
CRI: 90 min
CCT¹: 4000K
Center Beam.: 2545cd
Beam Angle: 22°

Efficacy: 80.2 lm/w

30° Horizontal Aiming

Distance		F.C.	Beam	
D	C		L	W
6	3.5	46	3.1	2.7
8	4.6	26	4.2	3.6
10	5.8	17	5.2	4.5
12	6.9	11	6.3	5.4

30° Horizontal Aiming

Distance		F.C.	Beam	
D	C		L	W
2	3.5	80	3.5	1.6
3	5.2	35	5.3	2.3
4	6.9	20	7.0	3.1
5	8.7	13	8.8	3.9

1. Correlated Color Temperature within specs as defined in ANSI_NEMA_ANSI C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
2. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

