



## V-FRAME



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately

Frame-in Kit	Cut-out	Required Clearance	Trim (see Reflector Trim specification sheets)
2002	3-3/4"	5"	Accepts all Incandescent 2000 Trims

### Features

**Mounting Frame:** 20 ga. (.032") galvanized steel. Four slots are positioned 90° apart to simplify alignment of luminaires.

**Rotoclips:** Easy reflector trim installation. Push-in / twist-out Rotoclips hold reflector flush to ceiling installation.

**Mounting Bars:** 20ga. galvanized steel. Lockable on frame-in kit. Extend from 14" (356mm) to 25" (635mm). Pre-installed integral nails for secure attachment to wood joists. Attaches to T-bar ceilings without the need of accessories.

**Snap-on Socket Cup:** .030 deep-draw galvanized steel. Adjustable to accommodate different lamps. Unitized optics assures accurate lamp positioning. Acts as a temporary work light during construction.

**Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with 18ga. SEW leads connected to junction box.

**Junction Box:** 4" (102mm) x 3" (76mm) x 2" (51mm) 18 ga.

galvanized steel. cULus certified for maximum of 8 No.12 ga. 90° C through branch circuit conductors. Pry-out knock-outs accept BX cable. Easy access from both sides with snap-on covers.

**Thermal Protector:** Meets cULus requirements. Insulation, if used, must be kept 3" (76mm) away from luminaire's sides and junction box.

### Accessories

**Thermal Protector replacement: 1970**

For all Incandescent Non-IC Frame-in Kits.

### Markings

cULus listed, suitable damp or wet location rated depending on Trim used.

