

Vaya Flood LP G3, RGBW

Low-power exterior architectural floodlight with intelligent RGBW light

Date: _____
Type: _____
Firm Name: _____
Project: _____

Vaya Flood LP G3, RGBW is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. Vaya Flood LP G3, RGBW adds a separate white LED creating better-quality whites compared to RGB. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Its integrated power connection and easily adjustable mounting brackets makes this product versatile and easy to use.

- Powerful - Throwing light with 10lx up to 42.7 m / 1fc up to 140 ft high, this narrow beam luminaire is a powerful solution for small- to mid-sized projects.
- Compact - The Vaya Flood series are compact, light-weight luminaires, combining an aluminium die-cast housing which is both anodized and powder coated to protect against corrosion, tempered glass, pressure equalizing air vents and IP66 outdoor rating, making the product robust against harsh outdoor environments.
- Simple - Direct line voltage (220 to 240 VAC) input eliminates the need for remote power supply unit, minimizing the system components and risk points, allowing for an easy and fast installation.



[Product page](#)

Beam Angles	10°, 20°, 40°
Lumens*	1,616 to 1,781
Efficacy	33.36 to 36.49
LED Channels	Red/Green/Blue/4000 K White
Environment	Dry/Damp/Wet Location, IP66

Input Voltage	220 to 240 VAC, 50/60 Hz
Power Consumption	48.8 W
Weight	2.6 kg (5.7 lb)
Housing Material	Die-cast aluminium, dark grey powder-coated finish
Approbations	CE

Specification Sheets

PDF Download	Beam Angle	Lumens	Item Number	12 NC
10°.CE	10°	1,781	316-100026-00	912400137393
20°.CE	20°	1,616	316-100026-01	912400137394
40°.CE	40°	1,644	316-100026-02	912400137395

* Lumen output measurements comply with IES LM-79-08 testing procedures.