

Vaya Linear MP G2, White

Second generation, powerful exterior line-voltage linear grazing luminaire with crisp white lighting

Date: _____
 Type: _____
 Firm Name: _____
 Project: _____

Vaya Linear MP G2 is a reliable and cost-effective LED wall grazing luminaire for both interior and exterior use that minimizes initial investment, while offering exceptional flexibility to create eye-catching wall washing and wall grazing effects. A wide range of color and CCT options, static on/off control, adjustable mounting brackets, wide or elliptical beam angles offer a comprehensive toolbox for your facade lighting needs. The discreet design with integrated power supply makes wiring simple, fast, and reliable.

- Powerful - Throwing light with 10lx up to 39 m / 1fc up to 128 ft (elliptical beam), the Linear MP is ideal for grazing of mid-sized walls and facades.
- Simple - Directly processes 100 to 277 VAC input, all in one slim housing, eliminating the need for bulky external low voltage power supplies and related cabling limitations, allowing for greater installation flexibility and a lean installation. Standard On-Off or custom DMX-512 control allows for dimming and dynamic control with industry standard protocols, allowing for easy setup and 3rd party system integration.



[Product page](#)

Beam Angles	10° x 50°, 50°
Lumens per foot*	993 - 1,101
Efficacy	64.8 - 81.9
CRI @ 3000 K†	81
CRI @ 4000 K†	82
Color Temperature [§]	3000 K, 4000 K
Applications	Wall Grazing

Input Voltage	100 to 277 VAC, 50/60 Hz
Weight	1.3 kg (2.9 lb) for 1 ft 3.6 kg (7.9 lb) for 4 ft
Housing Material	Extruded aluminium, dark grey anodized finish
Approbations	UL/cUL, FCC Class A, CE, PSE, CQC, RCM
Environment	Dry/Damp/Wet Location, IP66

3000 K Specification Sheets

Custom products information available

PDF Download	Beam Angle	Lumens*	Efficacy	CRI†	Power	Weight	Item Number	12 NC
3000 K, 10° x 50°, 0.3 m (1 ft), CE	10° x 50°	993	64.8	82	18 W	1.3 kg (2.9 lb)	350-000023-01	912400137147
3000 K, 10° x 50°, 0.3 m (1 ft), CE/CQC	10° x 50°	993	64.8	82	18 W	1.3 kg (2.9 lb)	350-000023-17	912400137163
3000 K, 10° x 50°, 0.3 m (1 ft), UL	10° x 50°	993	64.8	82	18 W	1.3 kg (2.9 lb)	350-000023-09	912400137155
3000 K, 10° x 50°, 1.2 m (4 ft), CE	10° x 50°	3,988	74.4	82	60 W	3.6 kg (7.9 lb)	350-000023-03	912400137149
3000 K, 10° x 50°, 1.2 m (4 ft), CE/CQC	10° x 50°	3,988	74.4	82	60 W	3.6 kg (7.9 lb)	350-000023-19	912400137165
3000 K, 10° x 50°, 1.2 m (4 ft), UL	10° x 50°	3,988	74.4	82	60 W	3.6 kg (7.9 lb)	350-000023-11	912400137157

COLOR KINETICS
 vaya series

3000 K Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Efficacy	CRI [†]	Power	Weight	Item Number	12 NC
3000 K, 50°, 0.3 m (1 ft), CE	50°	998	65.2	82	18 W	1.3 kg (2.9 lb)	350-000023-00	912400137146
3000 K, 50°, 0.3 m (1 ft), CE/CQC	50°	998	65.2	82	18 W	1.3 kg (2.9 lb)	350-000023-16	912400137162
3000 K, 50°, 0.3 m (1 ft), UL	50°	998	65.2	82	18 W	1.3 kg (2.9 lb)	350-000023-08	912400137154
3000 K, 50°, 1.2 m (4 ft), CE	50°	4,080	76.8	82	60 W	3.6 kg (7.9 lb)	350-000023-02	912400137148
3000 K, 50°, 1.2 m (4 ft), CE/CQC	50°	4,080	76.8	82	60 W	3.6 kg (7.9 lb)	350-000023-18	912400137164
3000 K, 50°, 1.2 m (4 ft), UL	50°	4,080	76.8	82	60 W	3.6 kg (7.9 lb)	350-000023-10	912400137156

4000 K Specification Sheets

PDF Download	Beam Angle	Lumens*	Efficacy	CRI [†]	Power	Weight	Item Number	12 NC
4000 K, 10° x 50°, 0.3 m (1 ft), CE	10° x 50°	1,072	69.5	81	18 W	1.3 kg (2.9 lb)	350-000023-05	912400137151
4000 K, 10° x 50°, 0.3 m (1 ft), CE/CQC	10° x 50°	1,072	69.5	81	18 W	1.3 kg (2.9 lb)	350-000023-21	912400137167
4000 K, 10° x 50°, 0.3 m (1 ft), UL	10° x 50°	1,072	69.5	81	18 W	1.3 kg (2.9 lb)	350-000023-13	912400137159
4000 K, 10° x 50°, 1.2 m (4 ft), CE	10° x 50°	4,378	80.1	81	60 W	3.6 kg (7.9 lb)	350-000023-07	912400137153
4000 K, 10° x 50°, 1.2 m (4 ft), CE/CQC	10° x 50°	4,378	80.1	81	60 W	3.6 kg (7.9 lb)	350-000023-23	912400137169
4000 K, 10° x 50°, 1.2 m (4 ft), UL	10° x 50°	4,378	80.1	81	60 W	3.6 kg (7.9 lb)	350-000023-15	912400137161
4000 K, 50°, 0.3 m (1 ft), CE	50°	1,098	71.1	81	18 W	1.3 kg (2.9 lb)	350-000023-04	912400137150
4000 K, 50°, 0.3 m (1 ft), CE/CQC	50°	1,098	71.1	81	18 W	1.3 kg (2.9 lb)	350-000023-20	912400137166
4000 K, 50°, 0.3 m (1 ft), UL	50°	1,098	71.1	81	18 W	1.3 kg (2.9 lb)	350-000023-12	912400137158
4000 K, 50°, 1.2 m (4 ft), CE	50°	4,402	81.9	81	60 W	3.6 kg (7.9 lb)	350-000023-06	912400137152
4000 K, 50°, 1.2 m (4 ft), CE/CQC	50°	4,402	81.9	81	60 W	3.6 kg (7.9 lb)	350-000023-22	912400137168
4000 K, 50°, 1.2 m (4 ft), UL	50°	4,402	81.9	81	60 W	3.6 kg (7.9 lb)	350-000023-14	912400137160

* Lumen output measurements comply with IES LM-79-08 testing procedures.

[‡] Correlated color temperature (CCT) complies with ANSI C78.377-2008 for the chromaticity of solid state lighting products.

[†] CRI refers to CRI Ra value, CRI R9 refers to R9 value in accordance with IESNA LM-79 standards.

COLORKINETICS vayaseries

© 2020 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/vaya