


Project:	Catalog No:	Mfg:
Location:	Fixture Type:	Qty:
Notes:		Lamps:



Catalog No.	Finishes	Mounting	Lamps	Accessories
6284 6285	Matte White Matte Black	All Lytespan Track Systems	55W-150W PAR-38 (Cool Beam Also) 45W-250W PAR-38 (Tungsten-Halogen) 150W Max w/ACC	4 3/4" Dia Series Color Filters, Heat Filter, Spread Lens, Louver and Wall Washer Accessory (see Lightolier Specification Sheets AL2HC

General Description

Minimal, functional form with cleanly detailed yoke and ring-shaped lampholder, uses 250W PAR-38 lamp for maximum compactness. Permanently-tensioned trunion mounting allows Lytespot to remain fixed at any angle. Unit adjusts horizontally up to 350°, vertically up to 90°. Regressed spring clips retain filters, spread lens, louver, and wall washer accessory.

Finish

All painted finishes baked enamel.

Electrical

Porcelain socket, medium base, nickel plated screw shell. No. 18 braided SF-1 leads.


Labels

UL; C.S.A.; I.B.E.W.

Patents

U.S. Patent No. 3,498,518. Foreign Patents granted

Lighting Data



LAMP	BEAM SPREAD (To 50% Max. Cp)	MAX C.P. (Candelas)	RATED LIFE (Hours)	0° AIMING ANGLE (A)				30° AIMING ANGLE (A)				45° AIMING ANGLE (A)				60° AIMING ANGLE (A)						
				DIST. ANCE (D)	F.C.	BEAM LGTH (L)	BEAM WIDTH (W)	DIST. ANCE (D)	DIST. ANCE (C)	F.C.	BEAM LGTH (L)	BEAM WIDTH (W)	DIST. ANCE (D)	DIST. ANCE (C)	F.C.	BEAM LGTH (L)	BEAM WIDTH (W)	DIST. ANCE (D)	DIST. ANCE (C)	F.C.	BEAM LGTH (L)	BEAM WIDTH (W)
100W PAR-38 SP	13°	6,500	2,000	6'	181	1.4'	1.4'	5'	2.9'	169	1.5'	1.3'	3'	3.0'	255	1.4'	1.0'	2'	3.5'	203	1.9'	0.9'
				8'	102	1.8'	1.8'	7'	4.0'	86	2.1'	1.8'	5'	5.0'	92	2.3'	1.6'	3'	5.2'	90	2.8'	1.4'
				10'	65	2.3'	2.3'	9'	5.2'	52	2.7'	2.4'	7'	7.0'	47	3.2'	2.3'	4'	6.9'	51	3.8'	1.8'
				12'	45	2.7'	2.7'	11'	6.4'	35	3.4'	2.9'	9'	9.0'	28	4.2'	2.9'	5'	8.7'	33	4.7'	2.3'

For 55W PAR-38 SP (Eng. Sav.), multiply F.C. above by 0.55. For 65W PAR-38 SP (Eng. Sav.), and 75W PAR-38 SP, multiply F.C. above by 0.80. For 80W and 85W PAR-38 SP (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

100W PAR-38 FL	30°	2,400	2,000	4'	150	2.1'	2.1'	3'	1.7'	173	2.2'	1.9'	3'	3.0'	94	3.5'	2.3'	1'	1.7'	300	2.7'	1.1'
				6'	67	3.2'	3.2'	5'	2.9'	62	3.7'	3.1'	4'	4.0'	53	4.6'	3.0'	2'	3.5'	75	5.5'	2.1'
				8'	37	4.3'	4.3'	7'	4.9'	32	5.1'	4.3'	5'	5.0'	34	5.8'	3.8'	3'	5.2'	33	8.2'	3.2'
				10'	24	5.4'	5.4'	9'	5.2'	19	6.6'	5.6'	6'	6.0'	24	6.9'	4.5'	4'	6.9'	19	10.9'	4.3'

For 55W PAR-38 FL (Eng. Sav.), multiply F.C. above by 0.55. For 65W PAR-38 FL (Eng. Sav.) and 75W PAR-38 FL, multiply F.C. above by 0.80. For 80W and 85W PAR-38 FL (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

90W PAR-38 NSP (T-H)	7°	19,000	2,000	10'	190	1.2'	1.2'	8'	4.6'	193	1.3'	1.1'	6'	5.0'	187	1.5'	1.0'	4'	6.9'	148	2.0'	1.0'
				15'	84	1.8'	1.8'	12'	6.9'	86	2.0'	1.7'	9'	9.0'	83	2.2'	1.6'	6'	10.4'	66	3.0'	1.5'
				20'	47	2.4'	2.4'	16'	9.2'	48	2.6'	2.3'	12'	12.0'	47	2.9'	2.1'	8'	13.9'	37	4.0'	2.0'
				25'	30	3.1'	3.1'	20'	11.5'	31	3.3'	2.8'	15'	15.0'	30	3.7'	2.6'	10'	17.3'	24	4.9'	2.4'

For 45W PAR-38 NSP (T-H), multiply F.C. above by 0.45. (L) and (W) remain the same.

90W PAR-38 SP (T-H)	12°	12,000	2,000	8'	187	1.7'	1.7'	7'	4.0'	159	2.0'	1.7'	5'	5.0'	170	2.1'	1.5'	3'	5.2'	167	2.6'	1.3'
				12'	83	2.5'	2.5'	10'	5.8'	78	2.8'	2.4'	7'	7.0'	87	3.0'	2.1'	4'	6.9'	94	3.5'	1.7'
				16'	47	3.4'	3.4'	13'	7.5'	46	3.7'	3.2'	9'	9.0'	52	3.8'	2.7'	5'	8.7'	60	4.3'	2.1'
				20'	30	4.2'	4.2'	16'	9.2'	30	4.5'	3.9'	11'	11.0'	35	4.7'	3.3'	6'	10.4'	42	5.2'	2.5'

For 45W PAR-38 SP (T-H), multiply F.C. above by 0.40. (L) and (W) remain the same.

90W PAR-38 FL (T-H)	30°	4,000	2,000	6'	111	3.2'	3.2'	5'	2.9'	104	3.7'	3.1'	3'	3.0'	157	3.5'	2.3'	2'	3.5'	125	5.5'	2.1'
				8'	62	4.3'	4.3'	7'	4.0'	53	5.1'	4.3'	5'	5.0'	57	5.8'	3.8'	3'	5.2'	56	8.2'	3.2'
				10'	40	5.4'	5.4'	9'	5.2'	32	6.6'	5.6'	7'	7.0'	29	8.1'	5.3'	4'	6.9'	31	10.9'	4.3'
				12'	28	6.4'	6.4'	11'	6.4'	21	8.1'	6.8'	9'	9.0'	17	10.4'	6.8'	5'	8.7'	20	13.7'	5.4'

For 45W PAR-38 FL (T-H), multiply F.C. above by 0.45. (L) and (W) remain the same.

150W PAR-38 SP	14°	10,500	2,000	8'	164	2.0'	2.0'	7'	4.0'	139	2.3'	2.0'	5'	5.0'	148	2.5'	1.7'	3'	5.2'	146	3.1'	1.5'
				12'	73	2.9'	2.9'	10'	5.8'	68	3.3'	2.8'	7'	7.0'	76	3.5'	2.4'	4'	6.9'	82	4.1'	2.0'
				16'	41	3.9'	3.9'	13'	7.5'	40	4.3'	3.7'	9'	9.0'	46	4.5'	3.1'	5'	8.7'	53	5.1'	2.5'
				20'	26	4.9'	4.9'	16'	9.2'	27	5.3'	4.5'	11'	11.0'	31	5.5'	3.8'	6'	10.4'	36	6.2'	2.9'

For 120W PAR-38 SP (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

150W PAR-38 FL	30°	4,000	2,000	6'	111	3.2'	3.2'	5'	2.9'	104	3.7'	3.1'	3'	3.0'	157	3.5'	2.3'	2'	3.5'	125	5.5'	2.1'
				8'	62	4.3'	4.3'	7'	4.0'	53	5.1'	4.3'	5'	5.0'	57	5.8'	3.8'	3'	5.2'	56	8.2'	3.2'
				10'	40	5.4'	5.4'	9'	5.2'	32	6.6'	5.6'	7'	7.0'	29	8.1'	5.3'	4'	6.9'	31	10.9'	4.3'
				12'	28	6.4'	6.4'	11'	6.4'	21	8.1'	6.8'	9'	9.0'	17	10.4'	6.8'	5'	8.7'	20	13.7'	5.4'

For 120W PAR-38 FL (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

150W PAR-38 SP (T-H)	13°	19,000	4,000	10'	190	2.3'	2.3'	8'	4.6'	193	2.4'	2.1'	6'	6.0'	187	2.8'	1.9'	4'	6.9'	148	3.8'	1.8'
				15'	84	3.4'	3.4'	12'	6.9'	86	3.7'	3.2'	9'	9.0'	83	4.2'	2.9'	6'	10.4'	66	5.7'	2.7'
				20'	47	4.6'	4.6'	16'	9.2'	48	4.9'	4.2'	12'	12.0'	47	5.5'	3.9'	8'	13.9'	37	7.6'	3.6'
				25'	30	5.7'	5.7'	20'	11.5'	31	6.1'	5.3'	15'	15.0'	30	6.9'	4.8'	10'	17.3'	24	9.5'	4.6'

For 120W PAR-38 SP (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

150W PAR-38 FL (T-H)	30°	4,900	4,000	6'	136	3.2'	3.2'	5'	2.9'	127	3.7'	3.1'	3'	3.0'	192	3.5'	2.3'	2'	3.5'	153	5.5'	2.1'
				8'	77	4.3'	4.3'	7'	4.0'	65	5.1'	4.3'	5'	5.0'	69	5.8'	3.8'	3'	5.2'	68	8.2'	3.2'
				10'	49	5.4'	5.4'	9'	5.2'	39	6.6'	5.6'	7'	7.0'	35	8.1'	5.3'	4'	6.9'	38	10.9'	4.3'
				12'	34	6.4'	6.4'	11'	6.4'	26	8.1'	6.8'	9'	9.0'	21	10.4'	6.8'	5'	8.7'	25	13.7'	5.4'

For 120W PAR-38 FL (Eng. Sav.), multiply F.C. above by 1.0. (L) and (W) remain the same.

250W PAR-38 SP (T-H)	9°	37,700	6,000	10'	377	1.6'	1.6'	8'	4.6'	383	1.7'	1.5'	6'	6.0'	370	1.9'	1.3'	4'	6.9'	295	2.6'	1.3'
				15'	168	2.4'	2.4'	12'	6.9'	170	2.5'	2.2'	9'	9.0'	165	2.9'	2.0'	6'	10.4'	100	10.8'	3.8'
				20'	94	3.1'	3.1'	16'	9.2'	96	3.4'	2.9'	12'	12.0'	93	3.8'	2.7'	8'	13.9'	74	5.1'	2.5'
				25'	60	3.9'	3.9'	20'	11.5'	61	4.2'	3.6'	15'	15.0'	59	4.8'	3.3'	10'	17.3'	47	6.4'	3.1'

250W PAR-38 FL (T-H)	35°	7,200	6,000	6'	200	3.8'	3.8'	5'	2.9'	187	4.3'	3.6'	3'	3.0'	283	4.2'	2.7'	2'	3.5'	225	7.2'	2.5'
				8'	112	5.0'	5.0'	7'	4.0'	95	6.1'	5.1'	5'	5.0'	102	7.0'	4.5'	3'	5.2'	100	10.8'	3.8'
				10'	72	6.3'	6.3'	9'	5.2'	58	7.8'	6.6'	7'	7.0'	52	9.8'	6.2'	4'	6.9'	56	14.4'	5.0'
				12'	50	7.6'	7.6'	11'	6.4'	39	9.6'	8.0'	9'	9.0'	31	12.6'	8.0'	5'	8.7'	36	18.0'	6.3'



©2015 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

Philips Lighting,
North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A Division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON,
Canada L6C 2S3
Tel. 800-668-9008