

# Urban

# **Optima**





# XL10 Post Top

Lumec Optima LED post top and pedant luminaires are the perfect choice for urban projects such as streets, walkways and public spaces that compel that extra little bit of detail. This timeless luminaire is made from top-quality materials, is easy to maintain, and adds a distinctive decorative aspect to any contemporary environment. Paired with the latest LED technology, its IP66 rating, multiple lumen outputs, various luminaire style options and energy-saving control options are well suited to meet wide range of project requirements.


Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

# Ordering guide

Series	LED module	Gen.	Globe	Optical system	Voltage	Driver options	Luminaire options		Poles/Brackets	Finish
XL10		G3								
2. Globe 3. Not a 4. Use c 5. If RCI The F	07 is required you	require option. ell or sho need to top of t	rting cap	is required to ensi C without cupola.		AST¹ Pre-set driver for progressive start-up CDMGE25¹ 8 hrs. 25% reduction CDMGE50¹ 8 hrs. 50% reduction CDMGE75¹ 6 hrs. 75% reduction CDMGM25¹ 6 hrs. 50% reduction CDMGM50¹ 6 hrs. 50% reduction CDMGM50¹ 6 hrs. 75% reduction CDMGM550¹ 4 hrs. 75% reduction CDMGS25¹ 4 hrs. 25% reduction CDMGS50¹ 4 hrs. 75% reduction CDMGS50¹ 7 hrs. 75% reduction CDMGS50¹ 9 hrs. 75% reduction CDMGS50¹ 1 hrs. 75% reduction CDMGS75¹ 1 hrs. 75% reduction CDMGS75¹ 2 hrs. 75% reduction CDMGS75¹ 3 hrs. 75% reduction CDMGS75¹ 4 hrs. 75% reduction CDMGS75¹ 5 hrs. 75% reduction CDMGS75¹ 6 hrs. 75%	CPT <sup>6</sup> Copper cupola CPTC <sup>6</sup> Varnished copper cupola HS House side shield PH8 <sup>6</sup> Photoelectric cell PH9 <sup>6</sup> Shorting cap PHXL <sup>6</sup> Photoelectric cell, extended life RC <sup>4,6</sup> Receptacle 3-pins SP2 (optional) 20kV/20kA surge protector TN2.875C 2-7/8" dia. tenon adaptor TN3 3" dia. tenon adaptor TN3.5 3-1/2" dia. tenon adaptor WC <sup>5</sup> without cupola	PR16 Decorative finial FN26 Decorative finial FN36 Decorative finial FN46 Decorative finial FN66 Decorative finial FN87 Decorative finial FN87 Decorative finial FN106 Decorative finial FN106 Decorative finial FN107 Decorative finial FN106 Decorative finial FN107 Decorative finial FN107 Decorative finial FN107 Decorative finial FN108 Decorative finial FN109 Decorat	Consult with Signify.com/ outdoorluminaires for details and the complete line of Signify poles and brackets.	Textured BE2TX Midnight Blue BE6TX Ocean Blue BE8TX Royal Blue BG2TX Sandstone BKTX Black BRTX Black BRTX Bronze GN4TX Blue Green GN6TX Forest Green GN8TX Dark Forest Green GY3TX Medium Grey RD2TX Burgundy RD4TX Scarlet WHTX White Other GR Gray Sandtex NP Natural Aluminum TG Hammertone Gol

# **Urban Luminaire**

#### **Dimensions**



# **LED Wattage and Lumen Values:** for XL10

			Average		LE2F			LE3F			LE4F			LE5F	
Ordering Code:	Total LEDs	current (mA)	System Wattage (W)	Lumen Output	BUG Rating	Efficacy (LPW)	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating	Lumen Output	Efficacy (LPW)	BUG Rating
Flat Lens 3000K	_														
35W32LED3K-G3-x	32	350	37	4781	B1-U0-G1	129	4689	B1-U0-G1	127	4682	B1-U0-G1	127	4500	B3-U0-G1	122
55W32LED3K-G3-x	32	530	54	6858	B2-U0-G1	127	6726	B1-U0-G1	125	6716	B1-U0-G2	124	6454	B3-U0-G1	120
72W32LED3K-G3-x	32	700	73	8649	B2-U0-G1	118	8483	B2-U0-G2	116	8470	B2-U0-G2	116	8140	B3-U0-G2	112
55W48LED3K-G3-x	48	350	54	7172	B2-U0-G1	133	7034	B1-U0-G1	130	7023	B1-U0-G2	130	6749	B3-U0-G1	125
80W48LED3K-G3-x	48	530	80	10287	B2-U0-G2	129	10090	B2-U0-G2	126	10074	B2-U0-G2	126	9681	B4-U0-G2	121
Flat Lens 4000K															
35W32LED4K-G3-x	32	350	37	5020	B1-U0-G1	136	4924	B1-U0-G1	133	4916	B1-U0-G1	133	4724	B3-U0-G1	128
55W32LED4K-G3-x	32	530	54	7201	B2-U0-G1	133	7063	B1-U0-G1	131	7052	B1-U0-G2	131	6777	B3-U0-G1	126
72W32LED4K-G3-x	32	700	73	9081	B2-U0-G1	124	8907	B1-U0-G2	122	8894	B1-U0-G2	122	8547	B3-U0-G2	117
55W48LED4K-G3-x	48	350	54	7530	B2-U0-G1	139	7386	B2-U0-G2	137	7375	B2-U0-G2	137	7087	B3-U0-G2	131
80W48LED4K-G3-x	48	530	80	10801	B2-U0-G2	135	10594	B2-U0-G2	132	10578	B2-U0-G2	132	10165	B4-U0-G2	127
Sag Lens 3000K															
35W32LED3K-G3-x	32	350	37	4808	B1-U0-G1	130	4688	B1-U0-G1	127	4681	B1-U0-G1	127	4541	B3-U0-G1	123
55W32LED3K-G3-x	32	530	54	6896	B2-U0-G1	128	6725	B1-U0-G2	125	6715	B1-U0-G2	124	6513	B3-U0-G2	121
72W32LED3K-G3-x	32	700	73	8698	B2-U0-G2	119	8481	B2-U0-G2	116	8468	B2-U0-G2	116	8214	B3-U0-G2	113
55W48LED3K-G3-x	48	350	54	7212	B2-U0-G1	134	7032	B1-U0-G2	130	7022	B1-U0-G2	130	6811	B3-U0-G2	126
80W48LED3K-G3-x	48	530	80	10345	B2-U0-G2	129	10087	B2-U0-G2	126	10072	B2-U0-G2	126	9770	B4-U0-G2	122
Sag Lens 4000K															
35W32LED4K-G3-x	32	350	37	5048	B1-U0-G1	136	4923	B1-U0-G1	133	4915	B1-U0-G1	133	4768	B3-U0-G1	129
55W32LED4K-G3-x	32	530	54	7241	B2-U0-G1	134	7061	B1-U0-G2	131	7050	B1-U0-G2	131	6839	B3-U0-G2	127
72W32LED4K-G3-x	32	700	73	9133	B2-U0-G1	125	8905	B1-U0-G2	122	8892	B1-U0-G2	122	8625	B3-U0-G2	118
55W48LED4K-G3-x	48	350	54	7572	B2-U0-G2	140	7384	B2-U0-G2	137	7373	B2-U0-G2	137	7152	B4-U0-G2	132
80W48LED4K-G3-x	48	530	80	10862	B2-U0-G2	136	10591	B2-U0-G2	132	10575	B2-U0-G2	132	10258	B4-U0-G2	128
Prism Globe 3000K		,													
35W32LED3K-G3-x	32	350	37	4895	B1-U3-G1	132	4679	B1-U3-G1	126	4655	B1-U3-G1	126	-	-	_
55W32LED3K-G3-x	32	530	54	7021	B2-U3-G2	130	6711	B1-U3-G2	124	6677	B1-U3-G2	124	-	_	_
72W32LED3K-G3-x	32	700	73	8855	B2-U3-G2	121	8464	B2-U3-G2	116	8420	B2-U3-G2	115	-	-	_
55W48LED3K-G3-x	48	350	54	7342	B2-U3-G2	136	7018	B1-U3-G2	130	6982	B1-U3-G2	129	-	-	-
80W48LED3K-G3-x	48	530	80	10532	B3-U3-G3	132	10066	B2-U3-G2	126	10015	B2-U3-G2	125	_	-	_
Prism Globe 4000K															
35W32LED4K-G3-x	32	350	37	5140	B2-U3-G2	139	4913	B1-U3-G1	133	4887	B1-U3-G2	132	-	-	_
55W32LED4K-G3-x	32	530	54	7372	B2-U3-G2	137	7046	B1-U3-G2	130	7010	B1-U3-G2	130	_	-	_
55W48LED4K-G3-x	48	350	54	9298	B2-U3-G2	172	8887	B2-U3-G2	165	8841	B2-U3-G2	164	-	_	_
72W32LED4K-G3-x	32	700	73	7709	B2-U3-G2	106	7369	B2-U3-G2	101	7331	B1-U3-G2	100	-	_	_
80W48LED4K-G3-x	48	530	80	11058	B3-U3-G3	138	10570	B2-U3-G2	132	10516	B2-U3-G2	131	_	_	_

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at signify.com/outdoorluminaires.

Note: Some data may be scaled based on tests of similar. But not identical luminaires.

# **Urban Luminaire**

# LED Wattage and Lumen Values: for XL10 with Sag lens

			Average	LE2S				LE3S			LE4S			LE5S		
Ordering Code: Sag lens (3000K)	Total LEDs		System Wattage <sup>1</sup> (W)	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating										
XL10-35W32LED3K-G2	32	350	37	3233	87	B1-U0-G1	3153	85	B1-U0-G1	3130	85	B1-U0-G1	3259	88	B2-U0-G1	
XL10-55W32LED3K-G2	32	530	54	4637	86	B1-U0-G1	4523	84	B1-U0-G1	4490	83	B1-U0-G1	4675	87	B3-U0-G1	
XL10-72W32LED3K-G2	32	700	73	5849	80	B1-U0-G1	5704	78	B1-U0-G1	5662	78	B1-U0-G2	5896	81	B3-U0-G1	
XL10-55W48LED3K-G2	48	350	54	4850	90	B1-U0-G1	4730	88	B1-U0-G1	4695	87	B1-U0-G1	4889	91	B3-U0-G1	
XL10-80W48LED3K-G2	48	530	80	6956	87	B1-U0-G1	6784	85	B1-U0-G2	6734	84	B1-U0-G2	7012	88	B3-U0-G2	

			Average		LE2S			LE3S			LE4S			LE5S		
Ordering Code: Sag lens (4000K)	Total LEDs		System Wattage <sup>1</sup> (W)	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	Lumen Output²	Efficacy (LPW)	BUG Rating	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	
XL10-35W32LED4K-G2	32	350	37	3621	98	B1-U0-G1	3531	95	B1-U0-G1	3506	95	B1-U0-G1	3650	99	B3-U0-G1	
XL10-55W32LED4K-G2	32	530	54	5194	96	B1-U0-G1	5065	94	B1-U0-G1	5028	93	B1-U0-G2	5236	97	B3-U0-G1	
XL10-72W32LED4K-G2	32	700	73	6550	90	B1-U0-G1	6388	88	B1-U0-G2	6342	87	B1-U0-G2	6603	90	B3-U0-G2	
XL10-55W48LED4K-G2	48	350	54	5431	101	B1-U0-G1	5297	98	B1-U0-G1	5258	97	B1-U0-G2	5475	101	B3-U0-G1	
XL10-80W48LED4K-G2	48	530	80	7791	97	B2-U0-G2	7598	95	B1-U0-G2	7543	94	B1-U0-G2	7853	98	B3-U0-G2	

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at signify.com/outdoorluminaires.

Note: Some data may be scaled based on tests of similar. But not identical luminaires.

# **LED Wattage and Lumen Values**: for XL10 with Globe

				LE2A				LE3A			LE4A		
Ordering Code: Globe (3000K)	Total LEDs		System Wattage <sup>1</sup> (W)	Lumen Output²	Efficacy (LPW)	BUG Rating	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	Lumen Output²	Efficacy (LPW)	BUG Rating	
XL10-35W32LED3K-G2	32	350	37	2759	75	B1-U3-G1	2601	70	B1-U2-G1	2794	76	B1-U2-G1	
XL10-55W32LED3K-G2	32	530	54	3958	73	B1-U3-G1	3730	69	B1-U3-G1	4008	74	B1-U3-G1	
XL10-72W32LED3K-G2	32	700	73	4992	68	B1-U3-G1	4705	64	B1-U3-G1	5055	69	B1-U3-G2	
XL10-55W48LED3K-G2	48	350	54	4139	77	B1-U3-G1	3901	72	B1-U3-G1	4192	78	B1-U3-G1	
XL10-80W48LED3K-G2	48	530	80	5937	74	B1-U3-G1	5596	70	B1-U3-G1	6012	75	B1-U3-G2	

			Average	LE2A			LE3A			LE4A			
Ordering Code: Globe (4000K)	Total LEDs		System Wattage <sup>1</sup> (W)	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	Lumen Output <sup>2</sup>	Efficacy (LPW)	BUG Rating	Lumen Output²	Efficacy (LPW)	BUG Rating	
XL10-35W32LED4K-G2	32	350	37	3559	96	B1-U3-G1	2913	79	B1-U2-G1	3130	85	B1-U2-G1	
XL10-55W32LED4K-G2	32	530	54	5105	95	B1-U3-G1	4178	77	B1-U3-G1	4489	83	B1-U3-G2	
XL10-72W32LED4K-G2	32	700	73	6439	88	B1-U3-G1	5269	72	B1-U3-G1	5662	78	B1-U3-G2	
XL10-55W48LED4K-G2	48	350	54	5339	99	B1-U3-G1	4369	81	B1-U3-G1	4695	87	B1-U3-G2	
XL10-80W48LED4K-G2	48	530	80	7658	96	B2-U3-G2	6267	78	B1-U3-G2	6734	84	B1-U3-G2	

Actual performance may vary due to installation variables including optics, mounting/ceiling height, dirt depreciation, light loss factor, etc.; highly recommended to confirm performance with a layout - contact Applications at signify.com/outdoorluminaires.

Note: Some data may be scaled based on tests of similar. But not identical luminaires.

# **Urban Luminaire**

## **Specifications**

#### Housing

**Finial:** Decorative cast 356 aluminum, mechanically assembled.

**Cupola:** Decorative spun aluminum 1100-0, mechanically mounted on hood.

**Hood**: Spun aluminum 1100 0 dome, mechanically assembled on the luminaire.

**Guard:** In a round shape with 4 arms, this guard is a one piece cast aluminum 356 welded to the fitter

### Access-mechanism

A die cast A360 aluminum technical ring with latch and hinge. The mechanism shall offer tool free access to the inside of the luminaire. An embedded memory retentive gasket shall ensure weatherproofing.

## Light engine

**LEDgine composed of 5 main components:** Heat Sink / Lens / LED lamp / Driver / Optical System. Electrical components are RoHS compliant.

## **LED** engine

Composed of high-performance white LEDs. Color temperature as per ANSI/NEMA bin Neutral White, 4000 Kelvin nominal (3985K +/-275K or 3710K to 4260K) or Warm white, 3000 Kelvin nominal (3045K +/- 175K or 2870K to 3220K), CRI 70 Min. 75 Typical.

#### Lens

**LExF / LExS:** Made of soda lime tempered glass lens, mechanically assembled and sealed onto the lower part of the heat sink.

**LExA (Globe):** Made of one-piece seamless injection-molded impact-resistant (DR) acrylic having an inner prismatic surface. The globe is mechanically assembled and sealed onto the lower part of the heat sink.

#### **Heat sink**

Made of cast aluminum optimizing the LEDs efficiency and life. Product does not use any cooling device with moving parts (only passive cooling device).

## Optical system

Composed of high performance optical grade PMMA acrylic refractor lenses to achieve desired distribution optimized to get maximum spacing, target lumens and a superior lighting uniformity. Optical system is rated IP66.

Performance shall be tested per LM 63, LM 79 and TM 15 (IESNA) certifying its photometric performance. Street side indicated.

Prismatic globe: IP66 rated optical system, composed of individual pre-oriented lens to achieve desired distribution, assembled with globe having an inner prismatic surface permanently sealed onto the lower part of the heat sink.

LE2A - Type II (ASYM) with globe (ACDR) LE3A - Type III (ASYM) with globe (ACDR) LE4A - Type IV (ASYM) with globe (ACDR)

Sag lens: IP66 rated optical system, composed of individual pre-oriented lens to achieve desired distribution, assembled with a tempered-glass sag lens permanently sealed onto the lower part of the heat sink.

LE2S - Type II (ASYM) with sag glass lens LE3S - Type III (ASYM) with sag glass lens LE4S - Type IV (ASYM) with sag glass lens LE5S - Type V (SYMM) with sag glass lens

Flat lens: IP66 rated optical system, composed of individual preoriented

lens to achieve desired distribution, assembled with a tempered-glass flat lens permanently sealed onto the lower part of the heat sink.

**LE2F** - Type II (ASYM) with flat glass lens **LE3F** - Type III (ASYM) with flat glass lens

**LE4F** - Type IV (ASYM) with flat glass lens

LE5F - Type V (SYMM) with flat glass lens

#### Driver

Driver comes standard with dimming compatible 0-10V. High power factor of 90% minimum. Electronic driver, operating range 50/60 Hz. Auto adjusting universal voltage input from 120 to 277 or 347 to 480 VAC rated for both application line to line or line to neutral, Class I, THD of 20% max. Maximum ambient operating temperature from 40°F (40°C) to 130°F (55°C). Certified in compliance to UL1310 cULus requirement. Dry and damp location. Assembled on a unitized removable tray with Tyco quick disconnect plug resisting to 221°F (105°C). The current supplying the LEDs will be reduced by the driver if the driver experiences internal overheating as a protection to the LEDs and the electrical components. Output is protected from short circuits, voltage overload and current overload. Automatic recovery after correction. Standard built in driver surge protection of 2.5kV (min).

### Surge protector

Surge protector tested in accordance with ANSI/IEEE C62.45 per ANSI/IEEE C62.41.2 Scenario I Category C High Exposure 10kV/10kA waveforms for Line Ground, Line Neutral and Neutral Ground, and in accordance with U.S. DOE (Department of Energy) MSSLC (Municipal Solid State Street Lighting Consortium) model specification for LED roadway luminaires electrical immunity requirements for High Test Level 10kV / 10kA. SP2 20kV/20kA optional.

## **Driver options**

**AST**: Pre-set driver for progressive start-up of the LED module(s) to optimize energy management and enhance visual comfort at start-up.

**CLO**: Pre-set driver to manage the lumen depreciation by adjusting the power given to the LEDs offering the same lighting intensity during the entire lifespan of the LED module.

**OTL**: Pre-set driver to signal end of life of the LED module(s) for better fixture management.

DMG: Dimmable driver 0-10V.

**CDMG:** Dynadimmer standard dimming functionalities including pre-programmed scenarios to suit many applications and needs from safety to maximum energy savings.

\* Contact factory for DALI options.

Order	Dimming									
Code	Scenario	Duration	Level							
CDMGS25	Safety	4 hours	25%							
CDMGS50	Safety	4 hours	50%							
CDMGS75	Safety	4 hours	75%							
CDMGM25	Median	6 hours	25%							
CDMGM50	Median	6 hours	50%							
CDMGM75	Median	6 hours	75%							
CDMGE25	Economy	8 hours	25%							
CDMGE50	Economy	8 hours	50%							
CDMGE75	Economy	8 hours	75%							

**SRD:** Sensor Ready Driver including SR communication (used for dimming and other functionalities), 24V auxiliary supply and a logical signal input (LSI) connected to the top NEMA twist lock receptacle.

**SRD1:** Sensor Ready Driver including SR communication (used for dimming and other functionalities) but with 24V auxiliary supply and a logical signal input (LSI) not connected to the top NEMA twist lock.

#### **LED Performance**

	Predict	ed lumen depi	reciation data¹			
Ambient Temperature (°C)	Driver mA	Calculated L <sub>70</sub> hours <sup>1,2</sup>	L <sub>70</sub> per TM-21 <sup>2,3</sup>	Lumen Maintenance % @ 60,000 hours		
25°C	700 mA	>100.000	>60.000	85%		

- Predicted performance derived from LED manufacturer's data and engineering design estimates,
   based on IESNA I M-80 methodology. Actual experience may vary due to field application conditions.
- based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. 2.  $L_{70}$  is the predicted time when LED performance depreciates to 70% of initial lumen output.
- 3. Calculated per IESNA TM21-11. Published  $L_{70}$  hours limited to 6 times actual LED test hours.

# **Urban Luminaire**

## Specifications (continued)

### Luminaire options

CPT Copper cupola

CPTC Varnished copper cupola

兌

FN2 Decorative finial

FN3 Decorative finial

FN4 Decorative finial



FN6 Decorative finial

<u>\$</u>

FN8 Decorative finial

 $\Omega$ 

FN9 Decorative finial

FN10 Decorative finial

**FNC** Decorative finial painted copper



**HS** House side shield



PH8
Photoelectric cell,
twist-lock type.
Allows 90° rotation



PH9 Shorting cap, twist-lock type



PHXL

Extended life Photoelectric cell, twist-lock type Allows 90° rotation



RC Receptacle 3-pins



RCD7 Receptacle 7-pins

SP2 20kV/10kA integral surge protector (optional)

WC Without Cupola



TN2.875C 2-7/8" dia. tenon adaptor



TN3 3" dia. tenon adaptor



TN3.5 3-1/2" dia. tenon adaptor

#### Fitter

Cast 356 aluminum c/w 4 set screws 3/8 16 UNC. This fitter holds 2 arms made of cast aluminum 356 mechanically assembled. Slip fits on a 4" (102mm) outside diameter X 4" (102mm) long tenon.

#### **Finish**

In accordance with the AAMA 2603 standard. Application of polyester powder coat paint (4 mils/100 microns) with +/- 1 mils/24 microns of tolerance. The Thermosetting resins provides a discoloration resistant finish in accordance with the ASTM D2244 standard, as well as luster retention in keeping with the ASTM D523 standard and humidity proof in accordance with the ASTM D2247 standard. The surface treatment achieves a minimum of 2000 hours for salt spray resistant finish in accordance with testing performed and per ASTM B117 standard.

# Textured Finish Options:

BE2TX: Textured Midnight Blue
BE6TX: Textured Ocean Blue
BE8TX: Textured Royal Blue
BG2TX: Textured Sandstone
BKTX: Textured Black
BRTX: Textured Block
BRTX: Textured Bronze
GN4TX: Textured Blue Green
GN6TX: Textured Forest Green
GN8TX: Textured Dark Forest Green

GNTX: Textured Green
GY3TX: Textured Medium Grey
RD2TX: Textured Burgundy
RD4TX: Textured Scarlet
WHTX: Textured White

#### **Non-Textured Finish Options:**

**GR**: Gray Sandtex **NP**: Natural Aluminum **TG**: Hammer-tone Gold

#### Luminaire useful life

Refer to IES files for energy consumption and delivered lumens for each option. Based on ISTMT in situ thermal testing in accordance with UL1598 and UL8750, using LM-80 data from LED manufacturers and engineering prediction methods, the luminaire useful life is expected to reach 100,000+ hours with >L70 lumen maintenance @ 25°C. Luminaire Useful Life accounts for LED lumen maintenance AND all of these additional factors including: LED life, driver life, PCB substrate, solder joints, on/off cycles, burning hours and corrosion. Entire luminaire is rated for operation in ambient temperature of -40°C / -40°F up to +35°C / +95°F.

#### **Hardware**

All exposed screws shall be complete with Ceramic primer-seal base coat to reduce seizing of the parts and offers a high resistance to corrosion. All seals and sealing devices are made and/or lined with EPDM and/or silicone and/or rubber.

#### Wiring

Gauge (#14) TEW/AWM 1015 or 1230 wires, 6" (152mm) minimum exceeding from luminaire.

## Quality control

Manufactured to ISO 9001 2008 standards and ISO 14001-2004 International Quality Standards Certification.

### **LED products** (manufacturing standard)

The electronic components sensitive to electrostatic discharge (ESD) such as light emitting diodes (LEDs) are assembled in compliance with IEC61340 5 1 and ANSI/ESD S20.20 standards so as to eliminate ESD events that could decrease the useful life of the product.

### Quality control


Manufactured to ISO 9001 2008 standards and ISO 14001-2004 International Quality Standards Certification.

# **Certifications and Compliance**

CSA, cULus Listed for Canada and USA Luminaires are DesignLights Consortium qualified.

# **Urban Luminaire**

## **Poles**



Consult Signify.com/outdoorluminaires for details and the complete line of Signify poles and brackets.

