

LEDALITE - TG RECESSED MICRO




by @ignify

TEST DATE: 05 Feb 2022 CATALOG NO: 2301L927NQBFF40xx


Lamp Type:	LED	Description:	BLK BTW LVR 4000LM DOWN 927
No. of Lamps:	96		
Rated Lamp Lumens:	-1	Flux (lm), Efficiency (%):	2771 lm 100%
Input Watts:	120 VAC 34.8	Up/Dn Ratio, Efficacy (lm/W):	100% Down / 0% Up 79.6
CIE-IES Classification:	Direct	Report:	LNG08493

CANDELA DISTRIBUTION						Flux
	0	22.5	45	67.5	90	Lumens
0	3199	3199	3199	3199	3199	
5	2945	3056	3172	3320	3427	300
15	2035	2291	2721	3398	3625	777
25	1117	1374	1774	2328	2418	824
35	551	672	796	996	971	514
45	288	304	281	338	335	245
55	144	146	101	83	45	96
65	8	9	12	6	4	13
75	3	2	1	3	2	2
85	1	1	1	1	0	1
90	0	0	0	0	0	
95	0	0	0	0	0	0
105	0	0	0	0	0	0
115	0	0	0	0	0	0
125	0	0	0	0	0	0
135	0	0	0	0	0	0
145	0	0	0	0	0	0
155	0	0	0	0	0	0
165	0	0	0	0	0	0
175	0	0	0	0	0	0
180	0	0	0	0	0	



CHARACTERISTICS						COEFFICIENTS OF UTILIZATION (%)											
RP1	Meets RP-1-12 recommendations for VDT-Critical spaces					Pc---	80				70			50			0
Direct: Peak Candela & Angle (0°)	3199.4		0.0			Pw---	70	50	30	10	70	50	30	50	30	10	0
Direct: Peak Candela & Angle (90°)	3689.8		12.5			RCR											
Spacing Criteria (0°, 90°, 180°)	0.61	0.99	N/A			0	119	119	119	119	116	116	116	111	111	111	100
Beam (H, V), Field (H, V)	56.9	37.2	88.0	82.0		1	113	111	108	106	111	108	106	104	102	101	93
Indirect: Peak Candela & Angle(°)	N/A		N/A			2	108	103	98	95	105	101	97	98	94	92	86
Indirect: Zenith Candela, Peak to Zenith	N/A		N/A			3	102	95	90	86	100	94	89	91	87	84	80
Luminous Width, Length, Height (ft)	0.13	4.00	0.00			4	97	89	83	79	95	88	82	86	81	77	74
DLC, UGR (4H x 8H, 1.0H), MDER	N/A		11.4	0.445		5	92	83	77	73	90	82	76	80	75	72	69
x, y, CCT, D _{uv}	0.4580	0.4092	2715	-0.0004		6	87	78	72	67	85	77	71	75	70	66	64
CRI (R _a), R _g , G _a , C _g	94	55	99	93		7	82	73	67	63	81	72	66	71	66	62	60
TM-30-18 R _f , R _g , R _h , R _z	92	90	100	-6%		8	78	69	63	58	77	68	62	67	62	58	56
120V: P(W), I(A), THD(%), PF	34.8	0.291	7.4	0.996		9	75	65	59	55	74	64	59	63	58	54	53
277V: P(W), I(A), THD(%), PF	34.7	0.129	12.7	0.966		10	71	61	55	51	70	61	55	60	55	51	50
347V: P(W), I(A), THD(%), PF	33.8	0.100	7.0	0.976		*Based on a floor reflectance of 0.2											

ZONAL LUMENS (lm)			
Zone	Lumens	%Fixture	%Lamp
0-30	1901	68.6%	68.6%
0-40	2415	87.1%	87.1%
0-60	2756	99.4%	99.4%
0-90	2771	100.0%	100.0%
90-130	0	0.0%	0.0%
90-150	0	0.0%	0.0%
90-180	0	0.0%	0.0%
0-180	2771	100.0%	100.0%










AVG LUMINANCE (cd/m ²)			
	0	45	90
0	66203	66203	66203
5	61170	65885	71183
15	43592	58294	77647
25	25510	40505	55200
35	13914	20100	24521
45	8428	8232	9797
55	5209	3629	1620
65	372	578	206
75	208	72	120
85	285	142	0

Output of GLA Calculation Tool for CIE 13.3 CRI and Associated CRI-based Colour Rendition Properties

Test Number:	T20201101	Manufacturer:	Ledalite by Signify
Date:	27 Aug 2020	Model:	TruGroove Suspended

Correlated Colour Temperature (T_{cp}) in K	2715	CIE1931 chromaticity coordinate, x	0.4580
Distance to Blackbody Locus (D_{uv})	-0.0004	CIE1931 chromaticity coordinate, y	0.4092
General Colour Rendering Index (R_a)	94	CIE1976 chromaticity coordinate, u'	0.2619
Red Rendering Index (R_9)	55	CIE1976 chromaticity coordinate, v'	0.5265
Colour Gamut Index (G_a)	99		
Red Chroma Index (C_9)	93		









ANSI/IES TM-30-18 Color Rendition Report

Source: T20201101

Date: 27 Aug 2020

Manufacturer: Ledalite by Signify

Model: TruGroove Suspended



Notes: This is a recommended method for displaying ANSI/IES TM-30-18 information.

x 0.4580

y 0.4092

u' 0.2619

v' 0.5265

SPECTRAL POWER DISTRIBUTION

λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD	λ (nm)	SPD
380	0.00020	425	0.00260	470	0.01850	515	0.04130	560	0.05830	605	0.08170	650	0.05160	695	0.01310	740	0.00310
381	0.00010	426	0.00290	471	0.01770	516	0.04170	561	0.05910	606	0.08240	651	0.04950	696	0.01270	741	0.00300
382	0.00010	427	0.00330	472	0.01700	517	0.04210	562	0.05960	607	0.08300	652	0.04870	697	0.01230	742	0.00290
383	0.00020	428	0.00370	473	0.01650	518	0.04250	563	0.05990	608	0.10830	653	0.04640	698	0.01180	743	0.00280
384	0.00010	429	0.00410	474	0.01630	519	0.04300	564	0.06060	609	0.10550	654	0.04430	699	0.01160	744	0.00270
385	0.00010	430	0.00460	475	0.01610	520	0.04330	565	0.06130	610	0.09270	655	0.04280	700	0.01120	745	0.00260
386	0.00010	431	0.00520	476	0.01600	521	0.04360	566	0.06160	611	0.09280	656	0.04180	701	0.01080	746	0.00250
387	0.00000	432	0.00580	477	0.01600	522	0.04410	567	0.06230	612	0.12620	657	0.04010	702	0.01040	747	0.00250
388	0.00010	433	0.00640	478	0.01630	523	0.04420	568	0.06290	613	0.15460	658	0.03860	703	0.01010	748	0.00240
389	0.00010	434	0.00720	479	0.01650	524	0.04470	569	0.06350	614	0.13510	659	0.03750	704	0.00980	749	0.00230
390	0.00010	435	0.00800	480	0.01690	525	0.04510	570	0.06430	615	0.10650	660	0.03690	705	0.00950	750	0.00220
391	0.00010	436	0.00900	481	0.01720	526	0.04550	571	0.06480	616	0.09200	661	0.03570	706	0.00920	751	0.00210
392	0.00010	437	0.01010	482	0.01770	527	0.04560	572	0.06520	617	0.08760	662	0.03420	707	0.00900	752	0.00210
393	0.00010	438	0.01140	483	0.01820	528	0.04590	573	0.06590	618	0.08730	663	0.03310	708	0.00870	753	0.00200
394	0.00010	439	0.01270	484	0.01870	529	0.04620	574	0.06660	619	0.08850	664	0.03210	709	0.00830	754	0.00200
395	0.00010	440	0.01460	485	0.01940	530	0.04640	575	0.06720	620	0.08590	665	0.03130	710	0.00810	755	0.00190
396	0.00020	441	0.01650	486	0.02000	531	0.04690	576	0.06760	621	0.08440	666	0.03060	711	0.00790	756	0.00180
397	0.00010	442	0.01860	487	0.02050	532	0.04700	577	0.06840	622	0.08290	667	0.02980	712	0.00760	757	0.00180
398	0.00010	443	0.02120	488	0.02120	533	0.04750	578	0.06880	623	0.08380	668	0.02940	713	0.00730	758	0.00170
399	0.00010	444	0.02380	489	0.02200	534	0.04770	579	0.06960	624	0.08490	669	0.02930	714	0.00710	759	0.00170
400	0.00010	445	0.02700	490	0.02270	535	0.04810	580	0.07020	625	0.08550	670	0.02890	715	0.00690	760	0.00170
401	0.00010	446	0.02980	491	0.02360	536	0.04830	581	0.07090	626	0.08610	671	0.02770	716	0.00660	761	0.00150
402	0.00010	447	0.03280	492	0.02430	537	0.04870	582	0.07170	627	0.08620	672	0.02650	717	0.00640	762	0.00160
403	0.00020	448	0.03520	493	0.02520	538	0.04910	583	0.07210	628	0.09230	673	0.02570	718	0.00620	763	0.00150
404	0.00020	449	0.03700	494	0.02620	539	0.04930	584	0.07290	629	0.12890	674	0.02480	719	0.00610	764	0.00140
405	0.00020	450	0.03870	495	0.02710	540	0.04970	585	0.07340	630	0.22960	675	0.02390	720	0.00580	765	0.00150
406	0.00030	451	0.03870	496	0.02790	541	0.05010	586	0.07410	631	0.24150	676	0.02320	721	0.00560	766	0.00140
407	0.00020	452	0.03780	497	0.02880	542	0.05040	587	0.07480	632	0.16910	677	0.02260	722	0.00550	767	0.00130
408	0.00030	453	0.03640	498	0.02980	543	0.05070	588	0.07520	633	0.11930	678	0.02180	723	0.00530	768	0.00130
409	0.00030	454	0.03420	499	0.03070	544	0.05120	589	0.07560	634	0.15470	679	0.02120	724	0.00510	769	0.00130
410	0.00040	455	0.03200	500	0.03170	545	0.05150	590	0.07610	635	0.18400	680	0.02060	725	0.00500	770	0.00120
411	0.00040	456	0.02980	501	0.03240	546	0.05180	591	0.07620	636	0.13430	681	0.02000	726	0.00480	771	0.00120
412	0.00050	457	0.02790	502	0.03320	547	0.05230	592	0.07690	637	0.09020	682	0.01930	727	0.00460	772	0.00110
413	0.00060	458	0.02640	503	0.03400	548	0.05290	593	0.07720	638	0.07050	683	0.01880	728	0.00450	773	0.00110
414	0.00070	459	0.02540	504	0.03490	549	0.05330	594	0.07740	639	0.06280	684	0.01810	729	0.00440	774	0.00100
415	0.00080	460	0.02450	505	0.03560	550	0.05340	595	0.07780	640	0.05940	685	0.01770	730	0.00420	775	0.00100
416	0.00090	461	0.02370	506	0.03630	551	0.05390	596	0.07870	641	0.05730	686	0.01720	731	0.00410	776	0.00100
417	0.00100	462	0.02370	507	0.03690	552	0.05430	597	0.08050	642	0.05590	687	0.01660	732	0.00400	777	0.00100
418	0.00110	463	0.02330	508	0.03740	553	0.05490	598	0.08090	643	0.05470	688	0.01620	733	0.00380	778	0.00100
419	0.00120	464	0.02300	509	0.03830	554	0.05540	599	0.08030	644	0.05400	689	0.01570	734	0.00370	779	0.00090
420	0.00140	465	0.02230	510	0.03870	555	0.05590	600	0.08040	645	0.05410	690	0.01520	735	0.00360	780	0.00090
421	0.00160	466	0.02180	511	0.03920	556	0.05620	601	0.08030	646	0.06440	691	0.01480	736	0.00340		
422	0.00180	467	0.02100	512	0.03990	557	0.05680	602	0.08080	647	0.08170	692	0.01430	737	0.00340		
423	0.00200	468	0.02010	513	0.04050	558	0.05730	603	0.08140	648	0.07340	693	0.01390	738	0.00330		
424	0.00230	469	0.01930	514	0.04080	559	0.05770	604	0.08170	649	0.05920	694	0.01360	739	0.00320		

UNIFIED GLARE RATING

Reflectances											
Ceiling Cavity		70	70	50	50	30	70	70	50	50	30
Walls		50	30	50	30	30	50	30	50	30	30
Floor Cavity		20	20	20	20	20	20	20	20	20	20
Room Size		UGR Viewed Crosswise					UGR Viewed Endwise				
X=2H	Y=2H	12.1	13.2	12.5	13.5	13.8	5.8	6.9	6.2	7.2	7.5
	3H	11.9	12.9	12.3	13.2	13.6	5.7	6.6	6.1	7.0	7.3
	4H	11.8	12.7	12.2	13.0	13.4	5.6	6.5	6.0	6.8	7.2
	6H	11.7	12.5	12.2	12.9	13.3	5.5	6.3	6.0	6.7	7.1
	8H	11.7	12.4	12.1	12.8	13.2	5.5	6.2	5.9	6.6	7.0
	12H	11.6	12.3	12.1	12.7	13.2	5.4	6.1	5.9	6.5	6.9
4H	2H	11.8	12.7	12.2	13.1	13.4	5.7	6.6	6.1	7.0	7.3
	3H	11.7	12.4	12.1	12.8	13.2	5.6	6.3	6.0	6.7	7.1
	4H	11.6	12.2	12.0	12.6	13.1	5.5	6.1	6.0	6.6	7.0
	6H	11.5	12.0	11.9	12.4	12.9	5.4	6.0	5.9	6.4	6.9
	8H	11.4	11.9	11.9	12.3	12.8	5.4	5.9	5.8	6.3	6.8
	12H	11.3	11.8	11.8	12.3	12.7	5.3	5.7	5.8	6.2	6.7
8H	4H	11.4	11.9	11.9	12.3	12.8	5.4	5.9	5.8	6.3	6.8
	6H	11.3	11.7	11.8	12.2	12.7	5.3	5.7	5.8	6.2	6.6
	8H	11.2	11.6	11.7	12.1	12.6	5.2	5.6	5.7	6.1	6.6
	12H	11.2	11.5	11.7	12.0	12.5	5.2	5.5	5.7	6.0	6.6
12H	4H	11.3	11.8	11.8	12.2	12.7	5.3	5.7	5.8	6.2	6.7
	6H	11.2	11.6	11.7	12.0	12.6	5.2	5.6	5.7	6.0	6.6
	8H	11.2	11.5	11.7	12.0	12.5	5.2	5.5	5.7	6.0	6.5

The UGR values have been calculated according to CIE Publ. 117.

Spacing-to-Height-Ratio = 1.00.

The highlighted value refers to the UGR value which the luminaire would have in a reference situation with room dimensions of 4H/8H and degrees of reflectance of 20% for the floor, 50% for the walls and 70% for the ceiling, as recommended by DLC.

The UGR value may vary depending on application specific parameters.