



Cleanroom LED CR250B

CR250B LED55S/840 PSU W60L60 IP65

Cleanroom LED CR250B, 63 W, 600x600 mm, 5500 lm, 4000 K, IP65

600x600 mm, Steel, White, Power supply unit (On/Off), 5500 lm, 63 W, 87 lm/W, 4000 K, (0.38, 0.38) SDCM <3, Opal, Tempered glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class II, Screw connector

Product data

General Information		Unified glare rating CEN	
Lamp family code	GRN55 [LED GreenLine 5500 lm]		22
Light source replaceable	Yes	Operating and Electrical	
Number of gear units	1 unit	Input Voltage	220-240 V
Driver included	Yes	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Inrush current	21 A
Value ladder	Performance	Inrush time	220 ms
Warranty period	5 years	Power Consumption	63 W
		Power Factor (Fraction)	0.9
		Connection	Screw connector
		Cable	-
		Number of products on MCB of 16 A type B	24
		Suitable for random switching	Yes
		Protection class IEC	Safety class II
		Total harmonic distortion	6 %

Cleanroom LED CR250B

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Tempered glass
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Opal
Overall length	595 mm
Overall width	595 mm
Overall height	135 mm
Dimensions (Height x Width x Depth)	135 x 595 x 595 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass with diffuser foil
Net Weight (Piece)	9.000 kg

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-5%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

Product Data


Order product name	CR250B LED55S/840 PSU W60L60 IP65
Full product name	CR250B LED55S/840 PSU W60L60 IP65
Full product code	871869607285100
Order code	910503910169
Material Nr. (12NC)	910503910169
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696072851
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696072851

Cleanroom LED CR250B

Dimensional drawing



Photometric data



Polar Normal (separate) - 910503910169

