



# Cleanroom LED CR250B

## CR250B LED35S/840 PSD W30L120 IP65

Cleanroom LED CR250B, 40 W, 1200x300 mm, 3500 lm, 4000 K, DALI, IP65

1200x300 mm, Steel, White, Power supply unit with DALI interface, 3500 lm, 40 W, 88 lm/W, 4000 K, (0.38, 0.38) SDCM <4, Opal, Tempered glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class II, Screw connector

### Product data

General Information		Operating and Electrical	
Lamp family code	GRN35 [LED GreenLine 3500 lm]	Luminaire light beam spread	110°
Light source replaceable	Yes	Unified Glare Rating (CEN)	22
Number of gear units	Unit	Input Voltage	220-240 V
Driver included	Yes	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Inrush current	4.6 A
Value ladder	Performance	Inrush time	750 ms
Warranty period	5 years	Power Consumption	40 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	3,500 lm	Connection	Screw connector
Correlated Colour Temperature (Nom)	4000 K	Cable	-
Luminous efficacy (rated) (nom.)	88 lm/W	Number of products on MCB (16 A type B)	24
Colour rendering index (CRI)	>80	Suitable for random switching	Yes
Number of light sources	2	Protection class IEC	Safety class II
Light source colour	840 neutral white		
Optic type	-		

# Cleanroom LED CR250B

Total harmonic distortion	6 %
---------------------------	-----

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

## Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover/lens material	Tempered glass
Fixation material	Stainless steel
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	1,195 mm
Overall width	295 mm
Overall height	135 mm
Dimensions (height x width x depth)	135 x 295 x 1195 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass with diffuser foil
Net Weight (Piece)	10.000 kg

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C

**Remarks** \* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED - based luminaires – January 2018; statistically there is no relevant difference in lumen maintenance between the B50 and, for

example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.38, 0.38) SDCM <4
Power consumption tolerance	+/-5%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤4

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.

## Product Data

Order product name	CR250B LED35S/840 PSD W30L120 IP65
Full product name	CR250B LED35S/840 PSD W30L120 IP65
Full EOC	871869607288200
Order code	910503910172
Material no. (12 NC)	910503910172
Local order code	CR250BL354D65
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696072882
Numerator – packs per outer box	1
EAN/UPC - Case	8718696072882

# Cleanroom LED CR250B

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910503910172

