



# Cleanroom LED CR250B

## CR250B LED55S/840 PSU W30L120 IP65

Cleanroom LED CR250B, 63 W, 1200x300 mm, 5500 lm, 4000 K, IP65

1200x300 mm, Steel, White, Power supply unit (On/Off), 5500 lm, 63 W, 87 lm/W, 4000 K, (0.38, 0.38) SDCM <3, Opal, Tempered glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class II, Screw connector

### Product data

General Information	
Lamp family code	GRN55 [LED GreenLine 5500 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years
Light Technical	
Luminous Flux	5,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	>80
Number of light sources	2
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	110°

Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	220 ms
Power Consumption	63 W
Power Factor (Fraction)	0.9
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	24
Suitable for random switching	Yes
Protection class IEC	Safety class II
Total harmonic distortion	6 %

# Cleanroom LED CR250B

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Tempered glass
Fixation material	Stainless steel
Housing Color	White
Optical cover finish	Opal
Overall length	1,195 mm
Overall width	295 mm
Overall height	135 mm
Dimensions (Height x Width x Depth)	135 x 295 x 1195 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Clear glass with diffuser foil
Net Weight (Piece)	10.000 kg

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-5%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

## Product Data

Order product name	CR250B LED55S/840 PSU W30L120 IP65
Full product name	CR250B LED55S/840 PSU W30L120 IP65
Full product code	871869607289900
Order code	910503910173
Material Nr. (12NC)	910503910173
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696072899
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696072899

# Cleanroom LED CR250B

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910503910173

