



# CoreLine Waterproof

## WT120C G2 LED40S/840 PSD L1200

CoreLine Waterproof, 30.5 W, L1200 mm, 4000 lm, 4000 K, DALI, Wide beam, Frosted, IP65, IK08, TW1-ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Operating and Electrical	
Lamp family code	LED40S [LED module, system flux 4000 lm]	Color rendering index (CRI)	>80
Light source replaceable	No	Light source color	840 neutral white
Number of gear units	1 unit	Optic type	Wide beam
Driver included	Yes	Luminaire light beam spread	105°
Service tag	Yes	Unified glare rating CEN	25
Lighting Technology	LED		
Value ladder	Performance	Input Voltage	220 to 240 V
Warranty period	5 years	Line Frequency	50 or 60 Hz
		Inrush current	19.4 A
		Inrush time	0.2 ms
		Power Consumption	30.5 W
		Power Factor (Fraction)	0.9
		Connection	Push-in connector 5-pole

# CoreLine Waterproof

Cable	-
Number of products on MCB of 16 A type B	30
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray
Optical cover finish	Frosted
Overall length	1,215 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 1215 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	1.530 kg

## Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70

## Sustainability Data


Sustainability rating	Unclassified
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts
Embedded carbon (A1-A3)	9.43 kg CO <sub>2e</sub>
Product non-virgin material ratio	10.7 %
Recyclable content ratio of the finished product	53.9 %
GWP total B6 (kg CO <sub>2eq</sub> ) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2eq</sub> / kWh)
GWP total B6 (kg CO <sub>2eq</sub> ) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2 eq</sub> / kWh)

## Product Data


Order product name	WT120C G2 LED40S/840 PSD L1200
Full product name	WT120C G2 LED40S/840 PSD L1200
Full product code	871869688309900
Order code	910505100053
Material Nr. (12NC)	910505100053
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696883099
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696883099
Product family code	WT130C [Coreline Waterproof G2 LSC]

# CoreLine Waterproof

## Dimensional drawing



## Photometric data



Polar Normal (separate) - WT120CI - 910505100053

