



# CoreLine Waterproof

## WT120C G2 LED34S/840 PSU ELB3 L1500

CoreLine Waterproof, 30 W, L1500 mm, 3400 lm, 4000 K, Wide beam, Frosted, IP65, IK08, TW1-ready, ELB3h

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Waterproof range of LED products can be used to replace traditional waterproof luminaires with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch. Also available as an Interact Ready wireless CoreLine waterproof luminaire that works with Interact Pro lighting software and Interact Ready devices to provide a connected lighting system for SMEs

### Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information	
Lamp family code	LED34S [LED module, system flux 3400 lm]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years

Light Technical	
Luminous Flux	3,400 lm
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	113 lm/W
Colour rendering index (CRI)	>80
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	105°
Unified Glare Rating (CEN)	25

# CoreLine Waterproof

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	5.16 A
Inrush time	0.047 ms
Power Consumption	30 W
Power Factor (Fraction)	0.86
Connection	Push-in connector 4-pole
Cable	-
Number of products on MCB (16 A type B)	36
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable
Mechanical and Housing	
Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Frosted
Overall length	1,515 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (height x width x depth)	76 x 80 x 1515 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	2.820 kg
Emergency Operation	
Emergency flux	500 lm
Rated duration of the emergency lighting (when fully charged)	3 h
Additional max. power consumption when emergency battery is charging	3 W
Central Emergency	No
Type of emergency lighting battery	Lithium
Emergency lighting	Emergency lighting 3-hours duration basic version
Emergency function testing method	Manual/Test button


Emergency lighting operation mode	Maintained
Approval and Application	
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED - based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	0 to +25 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70
Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	25.1 kg CO <sub>2</sub> e
Product non-virgin material ratio	15 %
Recyclable the content ratio of the finished product	53.7 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life

## CoreLine Waterproof


	(hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
<b>GWP total B6 (kg CO<sub>2</sub>eq) Functional Unit</b>	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO <sub>2</sub> eq / kWh)
<b>Product Data</b>	
<b>Order product name</b>	WT120C G2 LED34S/840 PSU ELB3 L1500
<b>Full product name</b>	WT120C G2 LED34S/840 PSU ELB3 L1500

<b>Full EOC</b>	871829185420300
<b>Order code</b>	910505100062
<b>Material no. (12 NC)</b>	910505100062
<b>Numerator – quantity per pack</b>	1
<b>EAN/UPC – Product/Case</b>	8718291854203
<b>Numerator – packs per outer box</b>	1
<b>EAN/UPC – Case</b>	8718291854203
<b>Product family code</b>	WT130C [Coreline Waterproof G2 LSC]

## Dimensional drawing



## Photometric data



Polar Normal (separate) - WT120CI - 910505100062

