



# CoreLine Waterproof

## WT120C G2 LED60S/840 PSD ELB3 L1500

CoreLine Waterproof, 49.5 W, L1500 mm, 6000 lm, 4000 K, DALI, Wide beam, Frosted, IP65, IK08, TW1-ready, ELB3h

L1500 mm, Polycarbonate, Grey, Power supply unit with DALI interface, 6000 lm, 49.5 W, 121 lm/W, 4000 K, (0.38,0.38)SDCM<=3, Wide beam, Frosted, Polycarbonate, IP65 | Dust penetration-protected, jet-proof, IK08 | 5 J vandal-protected, Safety class I, Push-in connector 6-pole, Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included), Emergency lighting 3-hours duration basic version

### Warnings and Safety

- UV radiation will damage the material over time, resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Operating and Electrical	
Lamp family code	LED60S [LED Module, system flux 6000 lm]	Luminous efficacy (rated) (nom.)	121 lm/W
Light source replaceable	No	Colour rendering index (CRI)	>80
Number of gear units	Unit	Light source colour	840 neutral white
Driver included	Yes	Optic type	Wide beam
Service Tag	Yes	Luminaire light beam spread	105°
Lighting Technology	LED	Unified Glare Rating (CEN)	25
Value ladder	Performance		
Warranty period	5 years	Input Voltage	220 to 240 V
		Line Frequency	50 or 60 Hz
		Inrush current	20.9 A
		Inrush time	0.192 ms
		Power Consumption	49.5 W

## CoreLine Waterproof

Power Factor (Fraction)	0.9
Connection	Push-in connector 6-pole
Cable	-
Number of products on MCB (16 A type B)	29
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Feed-through wiring	Simple connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)
Total harmonic distortion	20 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

### Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Grey
Optical cover/lens finish	Frosted
Overall length	1,515 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (height x width x depth)	76 x 80 x 1515 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Net Weight (Piece)	2.820 kg

### Emergency Operation

Emergency flux	500 lm
Rated duration of the emergency lighting (when fully charged)	3 h
Additional max. power consumption when emergency battery is charging	3 W
Central Emergency	No
Type of emergency lighting battery	Lithium
Emergency lighting	Emergency lighting 3-hours duration basic version
Emergency function testing method	Manual/Test button
Emergency lighting operation mode	Maintained

### Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces

CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED - based luminaires – January 2018'; statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Flickering value (PstLM)	1
Stroboscopic effect	1.6
Ambient temperature range	0 to +25 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L70

### Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	25.1 kg CO <sub>2</sub> e
Product non-virgin material ratio	15 %
Recyclable the content ratio of the finished product	53.7 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000

# CoreLine Waterproof


(lm) / LUMEN OUTPUT DECLARED UNIT (lm) \*  
35000 (hrs) \* ENERGY MIX (kg CO2 eq / kwh)

Material no. (12 NC)	910505100076
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696883143
Numerator – packs per outer box	1
EAN/UPC - Case	8718696883143
Product family code	WT130C [Coreline Waterproof G2 LSC]


## Product Data

Order product name	WT120C G2 LED60S/840 PSD ELB3 L1500
Full product name	WT120C G2 LED60S/840 PSD ELB3 L1500
Full EOC	871869688314300
Order code	910505100076

## Dimensional drawing



## Photometric data



Polar Normal (separate) - WT120CI - 910505100076

