



# PowerBalance RC360B

## RC362B 34S/940 PSD W62L62 VPC

PowerBalance RC360B, 26 W, 620x620 mm, VPC, 3400 lm, 4000 K, CRI>90, DALI, UGR19

When it comes to lighting office spaces with LED luminaires, businesses are willing to invest in sustainability, provided they get a payback on their investment. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. Philips PowerBalance Gen2 is our most energy-efficient, office-compliant LED luminaire. Designed for circularity and enhanced wellbeing, this office luminaire also promises future-proof connectivity. State-of-the-art efficacy (at CRI >90), upgradability features, a long lifetime, repairability, and design for recyclability make PowerBalance Gen2 a true 'green choice'. One that also delivers significantly lower operational costs to ensure an attractive payback that meets the needs of businesses and the specification market. The Gen2 architecture in the latest PowerBalance range has enabled us to create a range of highly-versatile modular and semi-modular luminaires. These LED luminaires can be easily mounted in ceilings with an exposed T-bar or concealed T-bar, as well as plaster ceilings and bandraaster-type ceilings. PowerBalance is a solution with superior lighting specifications combined with a best-in-class connectivity designed for Circularity & enhanced Wellbeing using Interact Pro - all with a sustainable approach to high-performance office lighting.

### Warnings and Safety

- The product is IP20 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed should be suitably checked
- If the advice above is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void

### Product data

# PowerBalance RC360B

General Information	
Lamp family code	LED34S [LED module, system flux 3400 lm]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
Serviceability class	Class B, luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge protection device, front cover and mechanical parts
Warranty period	5 years
Sustainability rating	Lighting for wellbeing

Light Technical	
Luminous Flux	3,400 lm
Saturated Red (R9)	>50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	129 lm/W
Color rendering index (CRI)	>90
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	940 neutral white
Optic type	Wide beam office compliant
Luminaire light beam spread	86°
Unified glare rating CEN	19

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Inrush current	23.1 A
Inrush time	0.221 ms
Power Consumption	26 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	22
UL Type	Type B - bypass the ballast
Suitable for random switching	No
Protection class IEC	Safety class I
Feed-through wiring	-
Total harmonic distortion	20 %

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

DALI Standard	DALI-2™
Maximum dim level	1%
Embedded control	-

Mechanical and Housing	
Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Opal
Reflector Finish	White reflector
Overall length	622 mm
Overall width	622 mm
Overall height	72 mm
Dimensions (Height x Width x Depth)	72 x 622 x 622 mm
Compatible ceiling or ceiling installation accessory type	Visible profile ceiling version
Optical finish	Opal
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK03 [0.35 J reinforced]
Explosion hazard class	-
Mounting	Recessed
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	4.900 kg

Emergency Operation	
Central Emergency	No

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3
Power consumption tolerance	+/-10%

# PowerBalance RC360B


Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5000 h	0.01 %
Control gear failure rate at median useful life 50000 h	2.5 %
Control gear failure rate at median useful life 100000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

<b>Product Data</b>	
Order product name	RC362B 34S/940 PSD W62L62 VPC
Full product name	RC362B 34S/940 PSD W62L62 VPC
Full product code	871869996454200
Order code	910505100248
Material Nr. (12NC)	910505100248
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699964542
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699964542
Product family code	RC362B [PowerBalance recessed]

## Dimensional drawing



## Photometric data



Polar Normal (separate) - RC460BN - 910505100248

## PowerBalance RC360B

