



# StoreSet Linear

## SM504T 66S/940 WIA DA35W WH

StoreSet Linear, track panel, 45 W, L1200 mm, 6700 lm, 4000 K, CRI>90, Wireless, Interact Ready, Double asymmetric optic 35° wide beam, Clear, White

StoreSet Linear is an ultra-flexible linear luminaire for retail track systems that offers excellent quality with the promise of future-proof upgrades. In retail applications such as supermarkets, city format shops, express stores, each linear panel can be combined with a wide range of spots from our portfolio, and integrated smoothly into your existing track system. So you can give your merchandise sparkle and stand out on the shelves, as well as in aisles and open areas. StoreSet Linear (SM504T) has a discreet, slim panel design that makes it easy to position the luminaires anywhere you like along the tracks - and accommodate future layout changes. Versions with a wireless driver offer enhanced comfort with dimming and scene setting on existing three-circuit track-mounted infrastructure without the need for wired controls. Plus integrated sensors for data collection will shed light on insightful, granular information that you can use to support your business.

### Warnings and Safety

- The canopy and optical surfaces must only ever be cleaned with a lint-free cloth and without detergents.

### Product data

General Information		Warranty period	
Light source replaceable	No		5 years
Number of gear units	1 unit	Light Technical	
Driver included	Yes	Luminous Flux	6,700 lm
Service tag	Yes	Saturated Red (R9)	>50
Lighting Technology	LED	Correlated Color Temperature (Nom)	4000 K
Value ladder	Specification	Luminous Efficacy (rated) (Nom)	145 lm/W

## StoreSet Linear

Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Light source color	940 neutral white
Optic type	Double asymmetric optic 35° wide beam
Luminaire light beam spread	104° x 98°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.23 ms
Power Consumption	45 W
Power Factor (Fraction)	0.9
Connection	Track
Cable	-
Number of products on MCB of 16 A type B	24
Suitable for random switching	Yes
Protection class IEC	Safety class I
Total harmonic distortion	20 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System ready
Control interface	Wireless
Constant light output	No
Maximum dim level	1%
Connectivity	Interact Ready

### Mechanical and Housing

Housing Material	Aluminum extruded
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Polyamide
Housing Color	White
Optical cover finish	Clear
Overall length	1,153 mm
Overall width	64 mm
Overall height	74 mm
Dimensions (Height x Width x Depth)	74 x 64 x 1153 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.800 kg

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM<3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	10 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	-

### Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.

Embedded carbon (A1-A3)	30.2 kg CO <sub>2e</sub>
Product non-virgin material ratio	8.36 %
Recyclable content ratio of the finished product	37.6 %
GWP total B6 (kg CO <sub>2eq</sub> ) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2eq</sub> / kWh)
GWP total B6 (kg CO <sub>2eq</sub> ) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2eq</sub> / kWh)

### Product Data


Order product name	SM504T 66S/940 WIA DA35W WH
Full product name	SM504T 66S/940 WIA DA35W WH
Full product code	872016901416900
Order code	910505102396
Material Nr. (12NC)	910505102396

## StoreSet Linear


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169014169
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169014169

Product family code	SM504T [STORESET LINEAR]
---------------------	--------------------------

### Dimensional drawing



### Photometric data



Polar Normal (separate) - SM504TI - 910505102396

