



StoreFlow

ST761T 49S/PW940 DIA BK

StoreFlow, Track flood (single), 38.5 W, 4900 lm, PremiumWhite, 4000 K, CRI>90, DALI, Interact Ready, Assymetric Beam angle, Black

Track flood (single), Aluminum, Black, Dali dimming Interact System ready, 4900 lm, 38.5 W, 128 lm/W, PremiumWhite, 4000 K, (0.374,0.364)<2, CRI>90, Assymetric Beam angle, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, 3C Track

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden.
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove
- With regards to damage factor, LED luminaires offer an improvement over conventional light sources, but may still cause color fading because even with no IR or UV in the light beam, light itself is a source of energy. To minimize the risk, avoid light levels over 1000 lx.
- ST761T Storeflow with 1 spotlight should always be installed in line with the track if a suspension wire is used. Installation under an angle is only allowed on a track with rigid suspension to avoid tilting the track

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years

Light Technical	
Luminous Flux	4,900 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	128 lm/W
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Light source color	PremiumWhite with CRI ≥90 and color temperature 4000K
Optic type	Assymetric Beam angle

Luminaire light beam spread	69° x 25°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	18 A
Inrush time	250 ms
Power Consumption	38.5 W
Power Factor (Fraction)	0.9
Connection	3C Track
Cable	-
Number of products on MCB of 16 A type B	34
Suitable for random switching	No
Protection class IEC	Safety class II
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Maximum dim level	1%
Connectivity	Interact Ready

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate aluminum coated
Optic material	Aluminum and polycarbonate
Optical cover material	-
Fixation material	-
Housing Color	Black
Optical cover finish	-
Overall length	132 mm
Overall width	104 mm
Overall height	229 mm
Overall diameter	0 mm
Dimensions (Height x Width x Depth)	229 x 104 x 132 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.800 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.5
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.374,0.364)<2
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	10 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data



Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	16.7 kg CO ₂ e
Product non-virgin material ratio	6.81 %
Recyclable content ratio of the finished product	57 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard
Product Data	
Order product name	ST761T 49S/PW940 DIA BK
Full product name	ST761T 49S/PW940 DIA BK
Full product code	872016901159500

StoreFlow


Order code	910505102521
Material Nr. (12NC)	910505102521
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169011595
Numerator - Packs per outer box	1

EAN/UPC - Case	8720169011595
Product family code	ST76IT [StoreFlow Single]

Dimensional drawing



Photometric data



Polar Normal (separate) - ST760TI - 910505102521

