



CoreLine Panel gen6

RC132V G6 36S/840 PSU W30L120 OC ELB3

CoreLine Panel gen6, 27 W, 1200x30 mm, VPC, 3600 lm, 4000 K, UGR19, ELB3h

Philips CoreLine panel Gen6 delivers on the CoreLine promise of innovation, easy installation, and excellent illumination. Designed as a direct replacement for functional luminaires in general lighting applications, this LED panel light's innovative All-in feature offers a choice of three lumen packages and three-color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Installing the CoreLine RC132V LED panel is quick and easy, using the product's quick connector or flywire. The CoreLine range includes Interact Ready luminaires with integrated wireless communications, ready to be used with Interact gateways, sensors, and software.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	133 lm/W
Service tag	Yes	Color rendering index (CRI)	>80
Value ladder	Performance	Beam angle of light source	90 degree(s)
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Light source color	840 neutral white
Warranty period	5 years	Optic type	Beam angle 90°
Sustainability rating	Unclassified	Luminaire light beam spread	90°
		Unified glare rating CEN	19
		All-in Type	All-in, Multi Color Temperature
Light Technical			
Luminous Flux	3,600 lm	Input Voltage	220-240 V
Saturated Red (R9)	80	Line Frequency	50 to 60 Hz

CoreLine Panel gen6

Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	16 A
Inrush time	0.2 ms
Power Consumption	27 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 4-pole
Cable	-
Number of products on MCB of 16 A type B	30
Suitable for random switching	No
Protection class IEC	Safety class II
Feed-through wiring	-
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Maximum dim level	Not applicable
Embedded control	-
Photocell	-

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	White reflector
Overall length	1,195 mm
Overall width	295 mm
Overall height	69 mm
Dimensions (Height x Width x Depth)	69 x 295 x 1195 mm
Compatible ceiling or ceiling installation accessory type	Visible profile ceiling version
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Explosion hazard class	-
Mounting	Ceiling
Safety device	SC [Safety cable]
Net Weight (Piece)	3.200 kg

Emergency Operation

Emergency flux	250 lm
Power consumption during Central DC emergency mode	2 W
Rated duration of the emergency lighting (when fully charged)	3 hour(s)

Additional max. power consumption when emergency battery is charging	6 W
Central Emergency	No
Type of emergency lighting battery	Lithium
Emergency lighting	Emergency lighting 3 hours duration basic version
Emergency function testing method	Manual / Test button
Emergency lighting operation mode	Maintained

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	0 °C to 35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Product Data


Order product name	RC132V G6 36S/840 PSU W30L120 OC ELB3
Full product name	RC132V G6 36S/840 PSU W30L120 OC ELB3
Full product code	872016958876900
Order code	58876900
Material Nr. (12NC)	910505102819
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169588769
Numerator - Packs per outer box	1

CoreLine Panel gen6


EAN/UPC - Case

8720169588769

Dimensional drawing



Photometric data



Polar Normal (separate) - RC132VI - 910505102819

