



GentleSpace gen4

BY581X 250S/840 SIA WB GC SI ELW3 H4

GentleSpace gen4, Highbay, 144 W, SMT, 25000 lm, 4000 K, Wireless, Interact Ready, Wide beam, H4, IP65, IK03, ELW3h

Highbay, Aluminium, Silver, Double layer powder coating, Suspension set twin, triangle, Sensor ready driver Interact System ready, Sensor SNH (R) 210, 25000 lm, 144 W, 174 lm/W, 4000 K, (0.380, 0.375) SDCM 3, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK03 | 0.3 J, Safety class I, Plug-in connector 5-pole Wieland/Adels compatible, Emergency lighting 3 hours duration with Wireless Interface

Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	25,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	174 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	91° x 91°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	-W;- W
Inrush current	5.1 A
Inrush time	0.76 ms
Power Consumption	144 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 5-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	12
Suitable for random switching	Yes (relates to presence/ movement detection and daylight harvesting)
Protection class IEC	Safety class I

GentleSpace gen4

Total harmonic distortion	20 %
---------------------------	------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Sensor ready driver Interact System ready
Control interface	Wireless
Constant light output	No
DALI Standard	DALI-2™ D4i™
Connectivity	Interact Ready
Embedded control	Sensor SNH (R) 210

Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Clear
Overall length	417 mm
Overall width	720 mm
Overall height	124 mm
Dimensions (Height x Width x Depth)	124 x 720 x 417 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK03 [0.3 J]
Mounting	Suspension set twin, triangle
Net Weight (Piece)	11.500 kg

Emergency Operation

Emergency flux	850 lm
Power consumption during Central DC emergency mode	5 W
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No
Type of emergency lighting battery	Lithium
Emergency lighting	Emergency lighting 3 hours duration with Wireless Interface
Emergency function testing method	Programmed automatic self testing via DALI or wireless lighting control system
Emergency lighting operation mode	Maintained

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

Stroboscopic effect visibility measure (SVM)	0.4
--	-----

Ambient temperature range	0 °C to 25 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.380, 0.375) SDCM 3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
--	------

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
---	---

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85
--	-----

Sustainability Data

Sustainability rating	Signify Circle
-----------------------	----------------

Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
--------------	--

Embedded carbon (A1-A3)	78.7 kg CO ₂ e
-------------------------	---------------------------

Product non-virgin material ratio	38.9 %
-----------------------------------	--------

Recyclable content ratio of the finished product	58.1 %
--	--------

GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
--	--

GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)
--	---

Product Data

Order product name	BY581X 250S/840 SIA WB GC SI ELW3 H4
--------------------	--------------------------------------

Full product name	BY581X 250S/840 SIA WB GC SI ELW3 H4
-------------------	--------------------------------------

Full product code	872016959405000
-------------------	-----------------

Order code	59405000
------------	----------

Material Nr. (12NC)	910505102869
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

EAN/UPC - Product/Case	8720169594050
------------------------	---------------

Numerator - Packs per outer box	1
---------------------------------	---


EAN/UPC - Case	8720169594050
----------------	---------------

Product family code	BY581X [Gentlespace gen4 Interact]
---------------------	------------------------------------

GentleSpace gen4


Dimensional drawing

BY581X suspended



With Wieland connector on a cable or free cable finish, cable length is: 0.5m or 1m or 1.5m or 2m

Photometric data



Polar Normal (separate) - BY580PI - 910505102869

