



# GentleSpace gen4

## BY580P 170S/840 PSU HE WB GC SI

GentleSpace gen4, Highbay, High efficiency, 97 W, SMT, 17000 lm, 4000 K, Wide beam, IP65, IK07

Highbay, Aluminium, Silver, Double layer powder coating, Suspension set twin, triangle, Power supply unit (On/Off), 17000 lm, 97 W, 175 lm/W, 4000 K, (0.383, 0.377) SDCM 3, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class I, Plug-in connector 3-pole Wieland/Adels compatible

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	17,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	91° x 91°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	-W;- W
Inrush current	7.68 A
Inrush time	0.06 ms
Power Consumption	97 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	12
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	20 %

# GentleSpace gen4

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Clear
Overall length	254 mm
Overall width	600 mm
Overall height	117 mm
Dimensions (Height x Width x Depth)	117 x 600 x 254 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Mounting	Suspension set twin, triangle
Net Weight (Piece)	6.300 kg

## Emergency Operation

Central Emergency	No
-------------------	----

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.04
Stroboscopic effect visibility measure (SVM)	0.07
Ambient temperature range	-30 to +55 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.383, 0.377) SDCM 3
Power consumption tolerance	+/-5%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
--	------

Lumen maintenance (EN-IEC 62722-2-1) - at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

## Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	49.1 kg CO <sub>2</sub> e
Product non-virgin material ratio	42.2 %
Recyclable content ratio of the finished product	60.8 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kwh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kwh)
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic


## Product Data

Order product name	BY580P 170S/840 PSU HE WB GC SI
Full product name	BY580P 170S/840 PSU HE WB GC SI
Full product code	872016959410400
Order code	59410400
Material Nr. (12NC)	910505102874
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169594104
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169594104
Product family code	BY580P [Gentlespace gen4 Small]

# GentleSpace gen4


## Dimensional drawing

BY580P, BY582P suspended



With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m or 2m

## Photometric data



Polar Normal (separate) - BY580PI - 910505102874

