



# GentleSpace gen4

## BY581P 350S/840 DIA HE MB GC SI

GentleSpace gen4, Highbay, High efficiency, 200 W, SMT, 35000 lm, 4000 K, DALI, Interact Ready, Medium beam, IP65, IK07

Highbay, Aluminium, Silver, Double layer powder coating, Suspension set twin, triangle, Dali dimming Interact System ready, 35000 lm, 200 W, 175 lm/W, 4000 K, (0.383, 0.377) SDCM 3, Medium beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class I, Plug-in connector 5-pole Wieland/Adels compatible

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	35,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Medium beam
Luminaire light beam spread	72° x 72°
Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	-W;- W
Inrush current	15.3 A
Inrush time	0.061 ms
Power Consumption	200 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 5-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	8
Suitable for random switching	No
Protection class IEC	Safety class I

# GentleSpace gen4

Total harmonic distortion	8 %
---------------------------	-----

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Maximum dim level	10%
Connectivity	Interact Ready

## Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Clear
Overall length	417 mm
Overall width	600 mm
Overall height	125 mm
Dimensions (Height x Width x Depth)	125 x 600 x 417 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Mounting	Suspension set twin, triangle
Net Weight (Piece)	10.800 kg

## Emergency Operation

Central Emergency	No
-------------------	----

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.22
Stroboscopic effect visibility measure (SVM)	0.01
Ambient temperature range	-30 to +55 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.383, 0.377) SDCM 3
Power consumption tolerance	+/-5%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) - at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

## Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	78.7 kg CO <sub>2</sub> e
Product non-virgin material ratio	38.9 %
Recyclable content ratio of the finished product	58.1 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)

## Product Data

Order product name	BY581P 350S/840 DIA HE MB GC SI
Full product name	BY581P 350S/840 DIA HE MB GC SI
Full product code	872016959441800
Order code	910505102906
Material Nr. (12NC)	910505102906
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169594418
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169594418
Product family code	BY581P [Gentlespace gen4 Large]

# GentleSpace gen4


## Dimensional drawing

BY581P, BY583P suspended



With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m, or 2m

## Photometric data



Polar Normal (separate) - BY580PI - 910505102906

