



# GentleSpace gen4

## BY581P 250S/840 DIA HE XNB GC SI

GentleSpace gen4, Highbay, High efficiency, 138 W, SMT, 25000 lm, 4000 K, DALI, Interact Ready, UGR19, Narrow beam, IP65, IK07

Highbay, Aluminium, Silver, Double layer powder coating, Suspension set twin, triangle, Dali dimming Interact System ready, 25000 lm, 138 W, 181 lm/W, 4000 K, (0.383, 0.377) SDCM 3, UGR19, Narrow beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class I, Plug-in connector 5-pole Wieland/Adels compatible

### Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	25,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	181 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Narrow beam
Luminaire light beam spread	28° x 28°
Unified glare rating CEN	19

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	-W;- W
Inrush current	5.1 A
Inrush time	0.76 ms
Power Consumption	138 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 5-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	16
Suitable for random switching	No
Protection class IEC	Safety class I

# GentleSpace gen4

Total harmonic distortion	20 %
---------------------------	------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Maximum dim level	10%
Connectivity	Interact Ready

## Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Clear
Overall length	417 mm
Overall width	600 mm
Overall height	125 mm
Dimensions (Height x Width x Depth)	125 x 600 x 417 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Mounting	Suspension set twin, triangle
Net Weight (Piece)	10.800 kg

## Emergency Operation

Central Emergency	No
-------------------	----

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.12
Stroboscopic effect visibility measure (SVM)	0.07
Ambient temperature range	-30 to +55 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.383, 0.377) SDCM 3
Power consumption tolerance	+/-5%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

## Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	78.7 kg CO <sub>2</sub> e
Product non-virgin material ratio	38.9 %
Recyclable content ratio of the finished product	58.1 %
GWP total B6 (kg CO <sub>2</sub> eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2</sub> eq / kWh)
GWP total B6 (kg CO <sub>2</sub> eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)

## Product Data

Order product name	BY581P 250S/840 DIA HE XNB GC SI
Full product name	BY581P 250S/840 DIA HE XNB GC SI
Full product code	872016958915500
Order code	58915500
Material Nr. (12NC)	910505102921
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169589155
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169589155
Product family code	BY581P [Gentlespace gen4 Large]

# GentleSpace gen4


## Dimensional drawing

BY581P, BY583P suspended



With Wieland connector on a cable or free cable finish, cable length is 0.5m or 1m or 1.5m or 2m

## Photometric data



Polar Normal (separate) - BY580PI - 910505102921

