



# TrueLine, surface mounted

## SM530C 68S/940 DEIA L2250 ALU

TrueLine, surface mounted, 48.5 W, 2250x55 mm; H88 mm, 6800 lm, 4000 K, CRI>90, DALI, Interact Ready, UGR19

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 174 lm/W and the option to upgrade to wireless connectivity and control.

### Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

General Information		Number of gear units	1 unit
Light source replaceable	No	Driver included	Yes

## TrueLine, surface mounted

Service tag	Yes
Lighting Technology	LED
Value ladder	Specification
Warranty period	5 years

### Light Technical

Luminous Flux	6,800 lm
Saturated Red (R9)	>50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	146 lm/W
Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Light source color	940 neutral white
Optic type	Wide beam
Luminaire light beam spread	80°
Unified glare rating CEN	19

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	25 A
Inrush time	230 ms
Power Consumption	48.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	29
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	20 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready external for central emergency lighting
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%
Connectivity	Interact Ready

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	-
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Aluminum
Optical cover finish	Frosted
Overall length	2,253 mm
Overall width	55 mm

Overall height	88 mm
Dimensions (Height x Width x Depth)	88 x 55 x 2253 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Mounting	Surface
Net Weight (Piece)	5.400 kg

### Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM) - Flickering value as 1 per EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	0.05 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

### Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and

## TrueLine, surface mounted


documentation are available for a period of time.

Material Nr. (12NC)	910505103255
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514972919
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514972919
Product family code	SM530C [TrueLine OC]


### Product Data

Order product name	SM530C 68S/940 DEIA L2250 ALU
Full product name	SM530C 68S/940 DEIA L2250 ALU
Full product code	871951497291900
Order code	910505103255

### Dimensional drawing



### Photometric data



Polar Normal (separate) - SM530CI - 910505103255

