



# CoreLine Downlight gen5

## DN142B 20S/830 WIA-E WR IP54

CoreLine Downlight gen5, 20.4 W, D200 mm, 2000 lm, 3000 K, Wireless, Interact Ready, White reflector, IP20/54

Philips CoreLine Downlight delivers on the CoreLine promise of innovative, easy to use and high-quality recessed downlights. The CoreLine Downlight range is suitable for one-to-one conventional luminaire replacements, with an attractive TCO that helps your customers make the switch to LED. These recessed indoor downlights offer uniform light distribution for use in general lighting and office applications (UGR 19). They also deliver instant energy savings and have a much longer lifetime, creating a solution that's environmentally friendly and real value-for-money. CoreLine DN142B recessed downlights are easy to install thanks to their standard cut-out size and push-in connectors. An Interact ready option with integrated wireless communications is also available in this family, which can be used with Interact gateways, sensors and software.

### Warnings and Safety

- Do not apply excessive force to the cable & DC connector, make sure the connector clip is locked before the power is on.

### Product data

General Information		Serviceability class	
Number of gear units	1 unit	Class C, luminaire without serviceable parts, not serviceable	
Driver included	Yes	Warranty period	
Service tag	Yes	5 years	
Mounting	Recessed	Sustainability rating	
Value ladder	Performance	Unclassified	
Light Technical			
Luminous Flux		2,000 lm	

## CoreLine Downlight gen5

Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source color	830 warm white
Optic type	White reflector perforated without louver
Luminaire light beam spread	84°
Unified glare rating CEN	25

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	10 A
Inrush time	0.002 ms
Power Consumption	20.4 W
Power Factor (Fraction)	0.95
Connection	-
Cable	2 cables 0.15m with connectors 2-pole
Number of products on MCB of 16 A type B	100
Suitable for random switching	Yes
Protection class IEC	Safety class II
Total harmonic distortion	35 %

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System ready external
Control interface	Wireless
Constant light output	No
Connectivity	Interact Ready

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	White reflector
Overall height	105 mm
Overall diameter	216 mm

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.560 kg

### Emergency Operation

Central Emergency	No
-------------------	----

### Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect visibility measure (SVM)	1
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.435,0.404) SDCM≤5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80

### Product Data


Order product name	DN142B 20S/830 WIA-E WR IP54
Full product name	DN142B 20S/830 WIA-E WR IP54
Full product code	872016910911700
Order code	910505103611
Material Nr. (12NC)	910505103611
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169109117
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169109117
Product family code	DN142B [CoreLine Downlight gen5]

# CoreLine Downlight gen5

## Dimensional drawing



## Photometric data



Polar Normal (separate) - DN142BI - 910505103611

