



TrueBlend Recessed

RC455B 36S/940 DLO W3W2 L1722 W185 B30

TrueBlend Recessed, 24 W, 1722x100 mm, B30, 3600 lm, 4000 K, CRI>90, UGR16, Wieland, TP(b), EL-DC

1722x100 mm, Steel, White, Signal white (RAL9003), Single layer powder coating, Mounting bracket - fixed height 30 mm - For C/U profiles, Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated), 3600 lm, 24 W, 150 lm/W, 4000 K, (0.38, 0.38) SDCM \leq 3.0, CRI>90, UGR16, Wide beam office compliant, White reflector, Diffused lens optic, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, GST18/3 Wieland/Adels for main + BST14/2 Wieland for DALI, TP(b) diffuser flammability class, DC operated central emergency lighting

Warnings and Safety

- The product is IP20 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Product data

General Information		Light Technical	
Lamp family code	36S [LED Module, system flux 3600 lm]	Upward light output ratio	0
Number of gear units	1 unit	Luminous Flux	3,600 lm
Driver included	Yes	Correlated Color Temperature (Nom)	4000 K
Light source engine type	LED	Luminous Efficacy (rated) (Nom)	150 lm/W
Service tag	Yes	Color rendering index (CRI)	>90
Value ladder	Specification	Light source color	940 neutral white
Warranty period	5 years	Optic type	Wide beam office compliant
		Luminaire light beam spread	76° x 74°

TrueBlend Recessed


Unified glare rating CEN	16
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	25.1 A
Inrush time	214 ms
Power Consumption	24 W
Power Factor (Fraction)	0.9
Connection	GST18/3 Wieland/Adels for main + BST14/2 Wieland for DALI
Cable	-
Number of products on MCB of 16 A type B	22
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	20 %
Wiring	
Connector Type	Wieland
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated)
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%
Embedded control	-
Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Diffused lens optic
Reflector Finish	White reflector
Overall length	1,722 mm
Overall width	185 mm
Overall height	90 mm
Dimensions (Height x Width x Depth)	90 x 185 x 1722 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Mounting	Mounting bracket - fixed height 30 mm - For C/U profiles
Optical cover type	Acrylic bowl/cover frosted
Net Weight (Piece)	5.390 kg

Emergency Operation	
Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting
Emergency lighting operation mode	Maintained
Approval and Application	
Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Diffuser Flammability Class	TP(b) diffuser flammability class
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3.0
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	2.5 %
Control gear failure rate at median useful life 100000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80
Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic
Product Data	
Order product name	RC455B 36S/940 DLO W3W2 L1722 W185 B30


TrueBlend Recessed

Full product name	RC455B 36S/940 DLO W3W2 L1722 W185 B30	EAN/UPC - Product/Case	8720169621633
Full product code	872016962163300	Numerator - Packs per outer box	1
Order code	62163300	EAN/UPC - Case	8720169621633
Material Nr. (12NC)	910505103939	Product family code	RC455B [TrueBlend Recessed Bandraster]
Numerator - Quantity Per Pack	1		

Dimensional drawing



Photometric data



Polar Normal (separate) - RC450BI - 910505103939

