



# TrueBlend Recessed

## RC455B 36S/940 MLO U4 W3 L1722 W100 B40

TrueBlend Recessed, 38 W, 1722x100 mm, B40, 3600 lm, 4000 K, CRI>90, Wireless, Interact Ready, UGR19, U4, Wieland, TP(b), EL-DC

1722x100 mm, Steel, White, Signal white (RAL9003), Single layer powder coating, Mounting bracket - fixed height 40 mm - For T/Omega profiles, Sensor ready driver Interact System ready for central emergency lighting, Upgradable sensor slot with SC200 sensor, 3600 lm, 38 W, 95 lm/W, 4000 K, (0.38, 0.38) SDCM  $\leq$ 3.0, CRI>90, UGR19, Wide beam office compliant, White reflector, Micro-lens optic, Polymethyl methacrylate, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, Plug-in connector 3-pole Wieland/Adels compatible, TP(b) diffuser flammability class, DC operated central emergency lighting

### Warnings and Safety

- The product is IP20 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

### Product data

| General Information      |                                       | Warranty period                    |          |
|--------------------------|---------------------------------------|------------------------------------|----------|
| Lamp family code         | 36S [LED Module, system flux 3600 lm] | 5 years                            |          |
| Number of gear units     | 1 unit                                | Light Technical                    |          |
| Driver included          | Yes                                   | Upward light output ratio          | 0        |
| Light source engine type | LED                                   | Luminous Flux                      | 3.600 lm |
| Service tag              | Yes                                   | Correlated Color Temperature (Nom) | 4000 K   |
| Value ladder             | Specification                         | Luminous Efficacy (rated) (Nom)    | 95 lm/W  |
|                          |                                       | Color rendering index (CRI)        | >90      |

## TrueBlend Recessed

|                             |                            |
|-----------------------------|----------------------------|
| Light source color          | 940 neutral white          |
| Optic type                  | Wide beam office compliant |
| Luminaire light beam spread | 76° x 74°                  |
| Unified glare rating CEN    | 19                         |

### Operating and Electrical

|  |   |
|--|---|
| Input Voltage                            | 220 to 240 V                                      |
| Line Frequency                           | 50 to 60 Hz                                       |
| Inrush current                           | 23 A  |
| Inrush time                              | 216 ms  |
| Power Consumption                        | 38 W  |
| Power Factor (Fraction)                  | 0.9   |
| Connection                               | Plug-in connector 3-pole Wieland/Adels compatible |
| Cable                                    | -   |
| Number of products on MCB of 16 A type B | 24  |
| Suitable for random switching            | Yes   |
| Protection class IEC                     | Safety class I                                    |
| Total harmonic distortion                | 20 %  |

### Wiring

|                |         |
|----------------|---------|
| Connector Type | Wieland |
|----------------|---------|

### Controls and Dimming

|                               |  |
|-------------------------------|--|
| Dimmable                      | Yes  |
| Driver/power unit/transformer | Sensor ready driver Interact System ready for central emergency lighting |
| Control interface             | Wireless   |
| Constant light output         | No   |
| Maximum dim level             | 1%   |
| Connectivity                  | Interact Ready   |
| Embedded control              | Upgradable sensor slot with SC200 sensor                                 |

### Mechanical and Housing

|                                     |  |
|-------------------------------------|--|
| Housing Material                    | Steel  |
| Reflector material                  | Steel  |
| Optic material                      | Polymethyl methacrylate                                      |
| Optical cover material              | Polymethyl methacrylate                                      |
| Fixation material                   | Steel  |
| Housing Color                       | White  |
| Mounting device                     | -  |
| Optical cover shape                 | Flat   |
| Optical cover finish                | Micro-lens optic   |
| Reflector Finish                    | White reflector  |
| Overall length                      | 1,722 mm   |
| Overall width                       | 100 mm   |
| Overall height                      | 90 mm  |
| Dimensions (Height x Width x Depth) | 90 x 100 x 1722 mm   |
| Ingress protection code             | IP20 [Finger-protected]                                      |
| Mech. impact protection code        | IK03 [0.3 J]   |
| Mounting                            | Mounting bracket - fixed height 40 mm - For T/Omega profiles |

|                    |                  |
|--------------------|------------------|
| Optical cover type | Micro-lens optic |
| Net Weight (Piece) | 5.390 kg         |

### Emergency Operation

|                                   |  |
|-----------------------------------|--|
| Central Emergency                 | Yes                                    |
| Emergency lighting                | DC operated central emergency lighting |
| Emergency lighting operation mode | Maintained                             |

### Approval and Application

|                                    |  |
|------------------------------------|--|
| Glow-wire test                     | Temperature 850 °C, duration 30 s              |
| Flammability mark                  | For mounting on normally flammable surfaces    |
| CE mark                            | Yes  |
| ENEC mark                          | ENEC mark                                      |
| Photobiological risk               | Photobiological risk group 1 @200mm to EN62778 |
| EU RoHS compliant                  | Yes  |
| Diffuser Flammability Class        | TP(b) diffuser flammability class              |
| Performance ambient temperature Tq | 25 °C  |
| Ambient temperature range          | +10 to +35 °C                                  |

### Initial Performance (IEC Compliant)

|                                       |                        |
|---------------------------------------|------------------------|
| Luminous flux tolerance               | +/-10%                 |
| Initial chromaticity                  | (0.38, 0.38) SDCM ≤3.0 |
| Power consumption tolerance           | +/-10%                 |
| Init. Color Rendering Index Tolerance | +/-2                   |

### Over Time Performance (IEC Compliant)

|  |       |
|--|-------|
| Control gear failure rate at median useful life 50000 h              | 2.5 % |
| Control gear failure rate at median useful life 100000 h             | 5 %   |
| Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h  | L90   |
| Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h | L80   |

### Sustainability Data

|  |   |
|--|---|
| Sustainability rating                      | Unclassified  |
| Repair class                               | Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time. |
| Non-virgin material ratio of the packaging | Cardboard > 80% recycled Plastic >35% recycled  |
| Packaging Recyclable content ratio         | Cardboard recycling rate > 80% Plastic recycling rate > 40%   |
| Packaging Material                         | Cardboard Plastic   |


# TrueBlend Recessed

## Product Data


|                     |   |
|---------------------|---|
| Order product name  | RC455B 36S/940 MLO U4 W3 L1722 W100 B40 |
| Full product name   | RC455B 36S/940 MLO U4 W3 L1722 W100 B40 |
| Full product code   | 872016962174900                         |
| Order code          | 62174900                                |
| Material Nr. (12NC) | 910505103950                            |

|                                 |   |
|---------------------------------|---|
| Numerator - Quantity Per Pack   | 1                                       |
| EAN/UPC - Product/Case          | 8720169621749                           |
| Numerator - Packs per outer box | 1                                       |
| EAN/UPC - Case                  | 8720169621749                           |
| Product family code             | RC455B [TrueBlend Recessed Bandrastrer] |

## Dimensional drawing



## Photometric data



Polar Normal (separate) - RC450BI - 910505103950

