



TrueBlend Recessed

RC455B 40S/940 MCB-M W3W2 L1722 W150 B30

TrueBlend Recessed, 38 W, 1722x100 mm, B30, 4000 lm, 4000 K, CRI>90, UGR16, Wieland, TP(b), EL-DC

1722x100 mm, Steel, White, Signal white (RAL9003), Single layer powder coating, Mounting bracket - fixed height 30 mm - For C/U profiles, Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated), 4000 lm, 38 W, 105 lm/W, 4000 K, (0.38, 0.38) SDCM \leq 3.0, CRI>90, UGR16, Reflector, White reflector, IP20 | Finger-protected, IK03 | 0.3 J, Safety class I, GST18/3 Wieland/Adels for main + BST14/2 Wieland for DALI, TP(b) diffuser flammability class, DC operated central emergency lighting

Warnings and Safety

- The product is IP20 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Product data

General Information	
Lamp family code	40S [LED module, system flux 4000 lm]
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Specification
Warranty period	5 years

Light Technical	
Upward light output ratio	0
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white
Optic type	Reflector
Luminaire light beam spread	50° x 60°

TrueBlend Recessed

Unified glare rating CEN	16
--------------------------	----

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	25.1 A
Inrush time	214 ms
Power Consumption	38 W
Power Factor (Fraction)	0.9
Connection	GST18/3 Wieland/Adels for main + BST14/2 Wieland for DALI
Cable	-
Number of products on MCB of 16 A type B	21
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	20 %

Wiring

Connector Type	Wieland
----------------	---------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible for central emergency lighting (integrated)
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%
Embedded control	-

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	-
Fixation material	Steel
Housing Color	White
Mounting device	-
Optical cover shape	Flat
Optical cover finish	-
Reflector Finish	White reflector
Overall length	1,722 mm
Overall width	150 mm
Overall height	90 mm
Dimensions (Height x Width x Depth)	90 x 150 x 1722 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Mounting	Mounting bracket - fixed height 30 mm - For C/U profiles
Optical cover type	-
Net Weight (Piece)	4.930 kg

Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting
Emergency lighting operation mode	Maintained

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Diffuser Flammability Class	TP(b) diffuser flammability class
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3.0
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	2.5 %
Control gear failure rate at median useful life 100000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic


Product Data

Order product name	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30
--------------------	---


TrueBlend Recessed

Full product name	RC455B 40S/940 MCB-M W3W2 L1722 W150 B30	EAN/UPC - Product/Case	8720169621916
Full product code	872016962191600	Numerator - Packs per outer box	1
Order code	62191600	EAN/UPC - Case	8720169621916
Material Nr. (12NC)	910505103967	Product family code	RC455B [TrueBlend Recessed Bandraster]
Numerator - Quantity Per Pack	1		

Dimensional drawing



Photometric data



Polar Normal (separate) - RC450BI - 910505103967

