



GreenSpace Evo Mini Adjustable

RS321B 20S/PW940 DIA-E HMB WH

GreenSpace Evo Mini Adjustable, Recessed accent, 3D printed, 16 W, D89 mm, 2150 lm, PremiumWhite, 4000 K, CRI>90, DALI, Interact Ready, High-reflective metal reflector Medium beam 20 to 40 degrees, PerfectAccent High-Efficacy reflector, White, IP20

Recessed accent, D89 mm, Polycarbonate, White, Recessed, Dali dimming Interact System ready external, 2150 lm, 16 W, 133 lm/W, PremiumWhite, 4000 K, (0.374, 0.364) SDCM <2, CRI>90, High-reflective metal reflector Medium beam 20 to 40 degrees, PerfectAccent High-Efficacy reflector, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, Push-in connector and pull relief

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Product data

General Information		Warranty period	
Number of gear units	1 unit	5 years	
Driver included	Yes	Light Technical	
Service tag	Yes	Luminous Flux	2,150 lm
Value ladder	Performance	Saturated Red (R9)	50

GreenSpace Evo Mini Adjustable

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	>90
Light source color	PremiumWhite with CRI ≥90 and color temperature 4000K
Optic type	High-reflective metal reflector Medium beam 20 to 40 degrees
Luminaire light beam spread	29°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	6.7 A
Inrush time	0.027 ms
Power Consumption	16 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	34
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready external
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Connectivity	Interact Ready

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	-
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	PerfectAccent High-Efficacy reflector
Overall height	82 mm
Overall diameter	100 mm
Nominal Ceiling cut-out diameter	89 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Mounting	Recessed
Net Weight (Piece)	0.400 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.374, 0.364) SDCM <2
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data



Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.

Product Data


Order product name	RS321B 20S/PW940 DIA-E HMB WH
Full product name	RS321B 20S/PW940 DIA-E HMB WH
Full product code	872016958998800
Order code	910505104502
Material Nr. (12NC)	910505104502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169589988
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169589988
Product family code	RS321B [GreenSpace Evo Mini Adjustable]

GreenSpace Evo Mini Adjustable

Dimensional drawing



Photometric data



Polar Normal (separate) - RS320BI - 910505104502

