

**BY580P 170S/840 DIA
HEWBGCSICHEMMBW1
mCW5**
910505104564



GentleSpace gen4, Highbay, 97 W, 17000 lm, 4000 K, DALI, Interact Ready, Wide beam, IP65, IK07

Highbay, Aluminium, Silver, Double layer powder coating, Dali dimming Interact System ready, 17000 lm, 97 W, 175 lm/W, 4000 K, (0.383, 0.377) SDCM 3, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK07 | 2 J reinforced, Safety class I, Plug-in connector 5-pole Wieland/Adels compatible

General Information

Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Value ladder	Specification
Warranty period	5 years

Light Technical

Luminous Flux	17,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	91° x 91°
Unified glare rating CEN	25
Melanopic Daylight Efficacy Ratio	0.65

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	-W;- W
Inrush current	4.5 A
Inrush time	1 ms
Power Consumption	97 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 5-pole Wieland/ Adels compatible
Cable	-
Number of products on MCB of 16 A type B	14
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Dali dimming Interact System ready
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™ with extended data: Parts 251/252/253
Maximum dim level	10%
Connectivity	Interact Ready

Mechanical and Housing

Housing Material	Aluminium
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Clear
Overall length	254 mm
Overall width	600 mm
Overall height	117 mm
Dimensions (Height x Width x Depth)	117 x 600 x 254 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2] reinforced]
Net Weight (Piece)	12.000 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-30 to +55 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.383, 0.377) SDCM 3
Power consumption tolerance	+/-5%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	-
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L85

Sustainability Data

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Embedded carbon (A1-A3)	49.1 kg CO ₂ e
Product non-virgin material ratio	42.2 %
Recyclable content ratio of the finished product	60.8 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)

GWP total B6 (kg CO2eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO2 eq / kwh)
--	--

Non-virgin material ratio of the packaging	Cardboard > 80% recycled
--	--------------------------

Packaging Recyclable content ratio	Cardboard recycling rate > 80%
------------------------------------	--------------------------------


Packaging Material	Cardboard
--------------------	-----------

Full product code	872016959060100
Order code	59060100
Material Nr. (12NC)	910505104564
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169590601
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169590601
Product family code	BY580P [Gentlespace gen4 Small]


Product Data

Order product name	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5
Full product name	BY580P 170S/840 DIA HEWBGCSICHEMMBW1mCW5

Dimensional drawing



Polar normal diagrams



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	GentleSpace-gen4-Manual-Instruction-v2024-10.pdf	Download 
Tender text	Tender_Text_910505104564_en_AE.txt	Download 
Installation Instructions	GentleSpace-gen4-MSP-SWP-Manual-Instruction-v2025-03.pdf	Download 
Photometry and lighting design	Document Name	Download
Revit file	Revit file - BY580PI - 910505104564.zip	Download 
LDT File	LDT File - BY580PI - 910505104564.ltd	Download 
ROLF File	ROLF File - BY580PI - 910505104564.rolfz	Download 
ULD File	ULD File - BY580PI - 910505104564.uld	Download 

