



GreenSpace Evo Mini Fixed

RS320B 7S/PW940 PSU-E HWB BK

GreenSpace Evo Mini Fixed, 3D printed, 6.8 W, C/O D79 mm, 850 lm, PremiumWhite, 4000 K, CRI>90, High-reflective metal reflector Medium beam 20 to 40 degrees, Black, IP20/54

GreenSpace Evo Mini Fixed is a miniaturized accent spot with a subtle and neutral design. This makes the product an ideal choice for fashion, hospitality and residential applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini Fixed a sustainable choice for accent lighting. The PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Renovation projects are easy with Perfect Fit due to the multiple cutout dimensions that are available. Further customization of colors, textures and Perfect Fit cutouts is possible via Philips MyCreation

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Product data

General Information		Driver included	Yes
Number of gear units	Unit	Service Tag	Yes

GreenSpace Evo Mini Fixed

Value ladder	Performance
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Warranty period	5 years
Sustainability rating	Signify Circle

Light Technical

Luminous Flux	850 lm
Saturated Red (R9)	50
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	126 lm/W
Colour rendering index (CRI)	>90
Light source colour	PremiumWhite with CRI ≥90 and colour temperature 4,000 K
Optic type	High-reflective metal reflector Medium beam 20 to 40 degrees
Luminaire light beam spread	36°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	14 A
Inrush time	0.13 ms
Power Consumption	6.8 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB (16 A type B)	65
Suitable for random switching	Not applicable
Protection class IEC	Safety class II
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Aluminium
Optic material	Aluminium
Optical cover/lens material	-

Fixation material	-
Housing Colour	Black
Optical cover/lens finish	-
Overall height	79 mm
Overall diameter	90 mm
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.400 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect	0.4
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.374, 0.364) SDCM <2
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Product Data


Order product name	RS320B 7S/PW940 PSU-E HWB BK
Full product name	RS320B 7S/PW940 PSU-E HWB BK
Full EOC	872016959070000
Order code	910505104582
Material no. (12 NC)	910505104582
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169590700
Numerator – packs per outer box	1
EAN/UPC – Case	8720169590700
Product family code	RS320B [GreenSpace Evo Mini Fixed]

GreenSpace Evo Mini Fixed

Dimensional drawing



Photometric data



Polar Normal (separate) - RS320BI - 910505104582

