



LuxSpace Compact, recessed

DN610B 20S/840UE PSU-E WR WH

LuxSpace Compact, recessed, UltraEfficient, 10.8 W, 2000 lm, 4000 K, UGR19, White reflector

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort, and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 185 lm/W, along with excellent color rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is. For office applications, LuxSpace offers dedicated tunable white luminaires with lighting controls for circadian lighting solutions and office-compliant versions (UGR19).

Product data

General Information		Color rendering index (CRI)	
Number of gear units	1 unit		>80
Driver included	Yes	Light source color	840 neutral white
Mounting	Recessed	Optic type	-
Value ladder	Specification	Luminaire light beam spread	-
Warranty period	5 years	Unified glare rating CEN	19
Sustainability rating	Unclassified		
Light Technical		Operating and Electrical	
Luminous Flux	2,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 to 60 Hz
Luminous Efficacy (rated) (Nom)	185 lm/W	Inrush current	12.78 A
		Inrush time	0.183 ms
		Power Consumption	10.8 W

LuxSpace Compact, recessed

Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	135
Suitable for random switching	No
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Plastic
Reflector material	Polycarbonate
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White
Optical cover finish	-
Reflector Finish	White reflector
Overall height	116 mm
Overall diameter	214 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Net Weight (Piece)	1.100 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes

ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38,0.38)
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90

Product Data


Order product name	DN610B 20S/840UE PSU-E WR WH
Full product name	DN610B 20S/840UE PSU-E WR WH
Full product code	872016983566500
Order code	910505104679
Material Nr. (12NC)	910505104679
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169835665
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169835665
Product family code	DN610B [LuxSpace Compact, recessed]

Dimensional drawing



LuxSpace Compact, recessed

Photometric data



Polar Normal (separate) - DN610BI - 910505104679

