



LuxSpace Compact, surface & suspended

DN610P 20S/840UE PSU-E WR WH

LuxSpace Compact, surface & suspended, downlight, UltraEfficient, 10.8 W, 1850 lm, 4000 K, UGR19

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort, and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 175 lm/W, along with excellent color rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is.

Product data

General Information		Operating and Electrical	
Number of gear units	1 unit	Luminaire light beam spread	-
Driver included	Yes	Unified glare rating CEN	19
Mounting	Surface	Input Voltage	220-240 V
Value ladder	Specification	Line Frequency	50 to 60 Hz
Warranty period	5 years	Inrush current	12.78 A
		Inrush time	0.183 ms
		Power Consumption	10.8 W
		Power Factor (Fraction)	0.9
		Connection	-
		Cable	-
		Number of products on MCB of 16 A type B	135
		Suitable for random switching	No
Light Technical			
Luminous Flux	1,850 lm		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	171 lm/W		
Color rendering index (CRI)	>80		
Light source color	840 neutral white		
Optic type	-		

LuxSpace Compact, surface & suspended

Protection class IEC	Safety class II
----------------------	-----------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Plastic
Reflector material	Polycarbonate
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White
Optical cover finish	-
Overall height	230 mm
Overall diameter	200 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.100 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38,0.38)
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90


Sustainability Data

Sustainability rating	Unclassified
Embedded carbon (A1-A3)	18.6 kg CO ₂ e
Product non-virgin material ratio	6.23 %
Recyclable content ratio of the finished product	27.2 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)

Product Data


Order product name	DN610P 20S/840UE PSU-E WR WH
Full product name	DN610P 20S/840UE PSU-E WR WH
Full product code	872016983771300
Order code	910505104881
Material Nr. (12NC)	910505104881
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169837713
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169837713
Product family code	DN610P [LuxSpace Pendant]

Dimensional drawing



LuxSpace Compact, surface & suspended

Photometric data



Polar Normal (separate) - DN610CI - 910505104881

