



LuxSpace Compact, surface & suspended

DN610P 20S/840UE PSU-E C SI

LuxSpace Compact, surface & suspended, downlight, UltraEfficient, 10.8 W, 2000 lm, 4000 K, UGR19

Philips LuxSpace is designed to provide the perfect combination of efficiency, high visual comfort, and stylish design without compromising on lighting performance. LuxSpace offers a long lifetime and efficacy of up to 175 lm/W, along with excellent color rendering and light distribution which have a major influence on the visual and non-visual effects of light on human health and well-being. The LuxSpace downlight family offers a wide choice of options for creating the desired ambience and supporting user comfort, no matter what the application is.

Product data

General Information	
Number of gear units	1 unit
Driver included	Yes
Mounting	Surface
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	185 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	-

Luminaire light beam spread	-
Unified glare rating CEN	19
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	12.78 A
Inrush time	0.183 ms
Power Consumption	10.8 W
Power Factor (Fraction)	0.9
Connection	-
Cable	-
Number of products on MCB of 16 A type B	135
Suitable for random switching	No

LuxSpace Compact, surface & suspended

Protection class IEC	Safety class II
----------------------	-----------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Plastic
Reflector material	Polycarbonate aluminum coated
Optic material	-
Optical cover material	-
Fixation material	-
Housing Color	White
Optical cover finish	-
Overall height	230 mm
Overall diameter	200 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	1.100 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38,0.38)
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90


Sustainability Data

Sustainability rating	Unclassified
Embedded carbon (A1-A3)	18.6 kg CO ₂ e
Product non-virgin material ratio	6.23 %
Recyclable content ratio of the finished product	27.2 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) /lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)

Product Data

Order product name	DN610P 20S/840UE PSU-E C SI
Full product name	DN610P 20S/840UE PSU-E C SI
Full product code	872016983777500
Order code	910505104887
Material Nr. (12NC)	910505104887
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169837775
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169837775
Product family code	DN610P [LuxSpace Pendant]

Dimensional drawing



LuxSpace Compact, surface & suspended

Photometric data



Polar Normal (separate) - DN610CI - 910505104887

