



# GreenSpace Evo Mini Wallmount

WL321W 12S/PW930 PSU HMB FG BK482

GreenSpace Evo Mini Wallmount, 10.3 W, 1.300 lm, 3000 K, CRI>90

GreenSpace Evo Mini Wallmount is a sustainable wall mounted fixture that comes with a sleek and subtle design. This makes the wallmount an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini wallmount a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customization of colors and textures is possible via Philips MyCreation

## Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth

## Product data

General Information		Sustainability rating	
Number of gear units	1 unit	Unclassified	
Driver included	Yes	Light Technical	
Value ladder	Specification	Luminous Flux	1.300 lm
Warranty period	5 years	Correlated Color Temperature (Nom)	3000 K
		Luminous Efficacy (rated) (Nom)	126 lm/W

# GreenSpace Evo Mini Wallmount

Color rendering index (CRI)	>90
Light source color	PremiumWhite with CRI ≥90 and color temperature 3000K
Optic type	High-reflective metal reflector Medium beam 20 to 40 degrees
Luminaire light beam spread	29°
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	4.2 A
Inrush time	0.072 ms
Power Consumption	10.3 W
Power Factor (Fraction)	0.90
Connection	Push-in connector 2-pole
Cable	-
Number of products on MCB of 16 A type B	65
Suitable for random switching	Not applicable
Protection class IEC	Safety class II

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	Tempered glass
Fixation material	-
Housing Color	Black
Optical cover finish	Clear
Overall length	90 mm
Overall height	230 mm
Overall diameter	65 mm

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.400 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.422, 0.386) SDCM <2
Power consumption tolerance	+/-10%


## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Product Data

Order product name	WL321W 12S/PW930 PSU HMB FG BK482
Full product name	WL321W 12S/PW930 PSU HMB FG BK482
Full product code	872016983794200
Order code	910505104905
Material Nr. (12NC)	910505104905
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169837942
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169837942

## Dimensional drawing




# GreenSpace Evo Mini Wallmount

## Photometric data

Light Distribution Diagram - WL321W 12S/PW930 PSU HMB FG BK482

Spectral Power Distribution Colour - WL321W 12S/PW930 PSU HMB FG BK482



Polar Normal (separate) - WL320WI - 910505104905

