

GreenSpace

DN500B 20S/840 PSU-E C BK

GreenSpace, 3D printed, 13.5 W, D150 mm, 2100 lm, 4000 K, High-gloss reflector, Clear, IP20

D150 mm, Plastic, Gray, Recessed, Power supply unit (On/Off), 2100 lm, 13.5 W, 157 lm/W, 4000 K, (0.38, 0.38) SDCM <3, High-gloss mirror, High-gloss reflector, Clear, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II

Product data

General Information		Line Frequency	
Number of gear units	1 unit		50 to 60 Hz
Gear	-	Inrush current	8.3 A
Driver included	Yes	Inrush time	23.5 ms
Value ladder	Specification	Power Consumption	13.5 W
Warranty period	5 years	Power Factor (Fraction)	0.90
		Connection	-
		Cable	-
Light Technical		Number of products on MCB of 16 A type B	58
Luminous Flux	2,100 lm	Suitable for random switching	No
Correlated Color Temperature (Nom)	4000 K	Protection class IEC	Safety class II
Luminous Efficacy (rated) (Nom)	157 lm/W		
Color rendering index (CRI)	80	Controls and Dimming	
Number of light sources	1	Dimmable	No
Light source color	840 neutral white	Driver/power unit/transformer	Power supply unit (On/Off)
Optic type	High-gloss mirror	Constant light output	No
Luminaire light beam spread	70°		
Unified glare rating CEN	22	Mechanical and Housing	
		Housing Material	Plastic
		Reflector material	Polycarbonate aluminum coated
Operating and Electrical			
Input Voltage	220 to 240 V		

Optic material	Polycarbonate
Optical cover material	-
Fixation material	-
Housing Color	Gray
Optical cover finish	Clear
Reflector Finish	High-gloss reflector
Overall height	73 mm
Overall diameter	180 mm
Nominal Ceiling cut-out diameter	150 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Mounting	Recessed
Net Weight (Piece)	0.600 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	10 %
Control gear failure rate at median useful life 50000 h	2 %
Control gear failure rate at median useful life 100000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80


Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	10.9 kg CO ₂ e
Product non-virgin material ratio	13.1 %
Recyclable content ratio of the finished product	47 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kwh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kwh)


Product Data

Order product name	DN500B 20S/840 PSU-E C BK
Full product name	DN500B 20S/840 PSU-E C BK
Full product code	872016983896300
Order code	83896300
Material Nr. (12NC)	910505105006
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169838963
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169838963
Product family code	DN500B [GreenSpace]

Dimensional drawing



Photometric data



Polar Normal (separate) - 910505105006

