



# GreenSpace

## DN500B 20S/840 PSU-E WR WH PCO

GreenSpace, 3D printed, 13.5 W, D150 mm, 1850 lm, 4000 K, White reflector, Opal, IP20/54

D150 mm, Plastic, Gray, Recessed, Power supply unit (On/Off), 1850 lm, 13.5 W, 138 lm/W, 4000 K, (0.38, 0.38) SDCM <3, High-gloss mirror, White reflector without louver, White reflector, Opal, Polycarbonate, IP54/20 | Dust accumulation protected, splash-proof/finger protected, IK02 | 0.2 J standard, Safety class II

### Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	1,850 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	138 lm/W
Color rendering index (CRI)	80
Number of light sources	1
Light source color	840 neutral white
Optic type	High-gloss mirror White reflector without louver
Luminaire light beam spread	110°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	8.3 A
Inrush time	23.5 ms
Power Consumption	13.5 W
Power Factor (Fraction)	0.90
Connection	-
Cable	-
Number of products on MCB of 16 A type B	58
Suitable for random switching	No
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Plastic
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Gray
Optical cover finish	Opal
Reflector Finish	White reflector
Overall height	73 mm
Overall diameter	180 mm
Nominal Ceiling cut-out diameter	150 mm
Ingress protection code	IP54/20 [Dust accumulation protected, splash-proof/finger protected]
Mech. impact protection code	IK02 [0.2 J standard]
Mounting	Recessed
Net Weight (Piece)	0.600 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	10 %
Control gear failure rate at median useful life 50000 h	2 %
Control gear failure rate at median useful life 100000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80
--	-----


Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	10.9 kg CO <sub>2e</sub>
Product non-virgin material ratio	13.1 %
Recyclable content ratio of the finished product	47 %
GWP total B6 (kg CO <sub>2eq</sub> ) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO <sub>2eq</sub> / kWh)
GWP total B6 (kg CO <sub>2eq</sub> ) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO <sub>2</sub> eq / kWh)

Product Data	
Order product name	DN500B 20S/840 PSU-E WR WH PCO
Full product name	DN500B 20S/840 PSU-E WR WH PCO
Full product code	872016983899400
Order code	83899400
Material Nr. (12NC)	910505105009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169838994
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169838994
Product family code	DN500B [GreenSpace]

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910505105009

