



GreenSpace

DN500B 20S/840 PSU-E OC WH PCC

GreenSpace, 3D printed, 13.5 W, D150 mm, 1950 lm, 4000 K, UGR19, High-gloss reflector, Clear, IP20/54

D150 mm, Plastic, Grey, Recessed, Power supply unit (On/Off), 1950 lm, 13.5 W, 146 lm/W, 4000 K, (0.38, 0.38) SDCM <3, UGR19, High-gloss mirror, High-gloss reflector, Clear, Polycarbonate, IP20/54 | Finger-protected; dust accumulation-protected, splash-proof, IK02 | 0.2 J standard, Safety class II

Product data

General Information	
Number of gear units	Unit
Gear	-
Driver included	Yes
Value ladder	Specification
Warranty period	5 years
Light Technical	
Luminous Flux	1,950 lm
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	146 lm/W
Colour rendering index (CRI)	80
Number of light sources	1
Light source colour	840 neutral white
Optic type	High-gloss mirror
Luminaire light beam spread	60°
Unified Glare Rating (CEN)	19

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	8.3 A
Inrush time	23.5 ms
Power Consumption	13.5 W
Power Factor (Fraction)	0.90
Connection	-
Cable	-
Number of products on MCB (16 A type B)	58
Suitable for random switching	No
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing material	Plastic
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	Grey
Optical cover/lens finish	Clear
Reflector finish	High-gloss reflector
Overall height	73 mm
Overall diameter	180 mm
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Mounting	Recessed
Net Weight (Piece)	0.600 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+10 to +35 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%


Over Time Performance (IEC Compliant)	
Driver failure rate at 5,000 hours	10 %
Control gear failure rate at median useful life 50,000 h	2 %
Control gear failure rate at median useful life 100,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90

Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80
--	-----


Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	10.9 kg CO ₂ e
Product non-virgin material ratio	13.1 %
Recyclable the content ratio of the finished product	47 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)

Product Data	
Order product name	DN500B 20S/840 PSU-E OC WH PCC
Full product name	DN500B 20S/840 PSU-E OC WH PCC
Full EOC	872016983900700
Order code	910505105010
Material no. (12 NC)	910505105010
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169839007
Numerator – packs per outer box	1
EAN/UPC – Case	8720169839007
Product family code	DN500B [GreenSpace]

Dimensional drawing



Photometric data



Polar Normal (separate) - 910505105010

