



CoreLine waterproof gen3

WT120C G3 27S/840 PSU TW3 L1200

CoreLine waterproof gen3, 17 W, L1200 mm, 2700 lm, 4000 K, Symmetrical, Clear, IP66, IK08, TW3, EL-ready

L1200 mm, Polycarbonate, Grey, Power supply unit (On/Off), 2700 lm, 17 W, 159 lm/W, 4000 K, (0.38, 0.37) SDCM<3, Symmetrical, Clear, Polycarbonate, IP66 | Dust penetration-protected, jet-proof, IK08 | 6 J, Safety class I, Push-in connector 5-pole, Feed-through wiring 3-phase, Self-contained emergency lighting is possible when used with a compatible battery kit accessory

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information		Luminaire light beam spread	
Number of gear units	1 unit	Luminaire light beam spread	110°
Driver included	Yes	Unified glare rating CEN	25
Warranty period	5 years	Operating and Electrical	
Light Technical		Input Voltage	220-240 V
Luminous Flux	2,700 lm	Line Frequency	0/50/60 Hz
Correlated Color Temperature (Nom)	4000 K	Inrush current	14.6 A
Luminous Efficacy (rated) (Nom)	159 lm/W	Inrush time	0.228 ms
Color rendering index (CRI)	>80	Power Consumption	17 W
Light source color	840 neutral white	Power Factor (Fraction)	0.90
Optic type	Symmetrical	Connection	Push-in connector 5-pole
		Cable	-

CoreLine waterproof gen3

Number of products on MCB of 16 A type B	34
Suitable for random switching	Yes
Protection class IEC	Safety class I
Feed-through wiring	Feed-through wiring 3-phase

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Grey
Optical cover finish	Clear
Overall length	1,235 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 1235 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Net Weight (Piece)	1.450 kg

Emergency Operation

Central Emergency	No
Emergency lighting	Self-contained emergency lighting is possible when used with a compatible battery kit accessory

Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect visibility measure (SVM)	0.4

Ambient temperature range	-20 °C to 40 °C
---------------------------	-----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+15%/-5%
Initial chromaticity	(0.38, 0.37) SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

Product Data

Order product name	WT120C G3 27S/840 PSU TW3 L1200
Full product name	WT120C G3 27S/840 PSU TW3 L1200
Full product code	872110335977300
Order code	35977300
Material Nr. (12NC)	910505106531
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103359773
Numerator - Packs per outer box	9
EAN/UPC - Case	8721103348722

CoreLine waterproof gen3

Dimensional drawing



Photometric data



Polar Normal (separate) - 910505106531

