



# CoreLine waterproof gen3

## WT120C G3 40S/840 PSD TW3 L1200

CoreLine waterproof gen3, 25 W, L1200 mm, 4000 lm, 4000 K, DALI, Symmetrical, Clear, IP66, IK08, TW3, EL-ready

L1200 mm, Polycarbonate, Grey, Power supply unit with DALI interface, 4000 lm, 25 W, 160 lm/W, 4000 K, (0.38, 0.37) SDCM<3, Symmetrical, Clear, Polycarbonate, IP66 | Dust penetration-protected, jet-proof, IK08 | 6 J, Safety class I, Push-in connector 7-pole, Feed-through wiring 3-phase, DC operated central emergency lighting, Self-contained emergency lighting is possible when used with a compatible battery kit accessory

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Optic type	
Number of gear units	1 unit	Optic type	Symmetrical
Driver included	Yes	Luminaire light beam spread	110°
Warranty period	5 years	Unified glare rating CEN	25
Light Technical		Operating and Electrical	
Luminous Flux	4,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	0/50/60 Hz
Luminous Efficacy (rated) (Nom)	160 lm/W	Inrush current	23.1 A
Color rendering index (CRI)	>80	Inrush time	0.221 ms
Light source color	840 neutral white	Power Consumption	25 W
		Power Factor (Fraction)	0.90

## CoreLine waterproof gen3

Connection	Push-in connector 7-pole
Cable	-
Number of products on MCB of 16 A type B	22
Suitable for random switching	Yes
Protection class IEC	Safety class I
Feed-through wiring	Feed-through wiring 3-phase

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Grey
Optical cover finish	Clear
Overall length	1,235 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 1235 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Net Weight (Piece)	1.540 kg

### Emergency Operation

Central Emergency	Yes
Emergency lighting	DC operated central emergency lighting Self-contained emergency lighting is possible when used with a compatible battery kit accessory

### Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark

EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+15%/-5%
Initial chromaticity	(0.38, 0.37) SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

### Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%
Packaging Material	Cardboard

### Product Data


Order product name	WT120C G3 40S/840 PSD TW3 L1200
Full product name	WT120C G3 40S/840 PSD TW3 L1200
Full product code	872110339008000
Order code	910505106562
Material Nr. (12NC)	910505106562
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103390080
Numerator - Packs per outer box	9
EAN/UPC - Case	8721103348999

# CoreLine waterproof gen3

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910505106562

