



# CoreLine waterproof gen3

## WT120C G3 35\_43\_51\_60S/865 PSU L1500

CoreLine waterproof gen3, All-in, 37.5 W, 21.5 W, L1500 mm, 3500 lm, 4300 lm, 5100 lm, 6000 lm, 6500 K, Symmetrical, Clear, IP66, IK08, EL-ready

L1500 mm, Polycarbonate, Grey, Power supply unit (On/Off), All-in, Multi Lumen, 3500 lm, 4300 lm, 5100 lm, 6000 lm, 37.5 W, 21.5 W, 162 lm/W, 159 lm/W, 6500 K, (0.31, 0.32) SDCM<3, Symmetrical, Clear, Polycarbonate, IP66 | Dust penetration-protected, jet-proof, IK08 | 6 J, Safety class I, Push-in connector 5-pole, Self-contained emergency lighting is possible when used with a compatible battery kit accessory

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		Light source color	
Number of gear units	1 unit	Light source color	865 cool daylight
Driver included	Yes	Optic type	Symmetrical
Warranty period	5 years	Luminaire light beam spread	110°
Light Technical		Unified glare rating CEN	25
Luminous Flux	3,500 4,300 5,100 6,000 lm	All-in Type	All-in, Multi Lumen
Correlated Color Temperature (Nom)	6500 K	Operating and Electrical	
Luminous Efficacy (rated) (Nom)	162 159 lm/W	Input Voltage	220-240 V
Color rendering index (CRI)	>80	Line Frequency	0/50/60 Hz
		Inrush current	24.5 A

## CoreLine waterproof gen3

Inrush time	0.136 ms
Power Consumption	37.5 21.5 W
Power Factor (Fraction)	0.95
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	35
Suitable for random switching	Yes
Protection class IEC	Safety class I
Feed-through wiring	-

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Grey
Optical cover finish	Clear
Overall length	1,515 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 1515 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Net Weight (Piece)	1.550 kg

### Emergency Operation

Central Emergency	No
Emergency lighting	Self-contained emergency lighting is possible when used with a compatible battery kit accessory

### Approval and Application

Glow-wire test	Temperature 850 °C, duration 30 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes

ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-20 °C to 40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+15%/-5%
Initial chromaticity	(0.31, 0.32) SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

### Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.

### Product Data

Order product name	WT120C G3 35_43_51_60S/865 PSU L1500
Full product name	WT120C G3 35_43_51_60S/865 PSU L1500
Full product code	872110339015800
Order code	39015800
Material Nr. (12NC)	910505106569
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103390158
Numerator - Packs per outer box	9
EAN/UPC - Case	8721103349064

# CoreLine waterproof gen3

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 910505106569

