



Maxos LED

4MX850 491 LED40S/840 PSD NB WH

Maxos LED, Trunking light panel, 24 W, L1478 mm, 4000 lm, 4000 K, DALI, Narrow beam, Clear, White, IP20

Trunking light panel, L1478 mm, Steel, White, Power supply unit with DALI interface, 4000 lm, 24 W, 166 lm/W, 4000 K, (0.38, 0.38) SDCM <3.5, Narrow beam, Clear, Polymethyl methacrylate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class I, Connection unit 5-pole

Product data

General Information	
Lamp family code	LED40S [LED module, system flux 4000 lm]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Service tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	166 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source color	840 neutral white

Optic type	Narrow beam
Luminaire light beam spread	50°
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.280 ms
Power Consumption	24 W
Power Factor (Fraction)	0.97
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	7 %

Maxos LED

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%

Mechanical and Housing	
Housing Material	Steel
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,478 mm
Overall width	63 mm
Overall height	50 mm
Dimensions (Height x Width x Depth)	50 x 63 x 1478 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polymethyl methacrylate bowl/cover
Net Weight (Piece)	1.700 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Ambient temperature range	-20 to +35 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤4
--	--------


Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) L90 at median useful life* 50000 h	
Lumen maintenance (EN-IEC 62722-2-1) L80 at median useful life* 100000 h	

Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	25.6 kg CO ₂ e
Product non-virgin material ratio	25.9 %
Recyclable content ratio of the finished product	50.3 %
GWP total B6 (kg CO ₂ eq) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO ₂ eq / kWh)
GWP total B6 (kg CO ₂ eq) Functional Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO ₂ eq / kWh)


Product Data	
Order product name	4MX850 491 LED40S/840 PSD NB WH
Full product name	4MX850 491 LED40S/840 PSD NB WH
Full product code	403073266166499
Order code	66166499
Material Nr. (12NC)	910629121726
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732661664
Numerator - Packs per outer box	3
EAN/UPC - Case	4030732258390
Product family code	4MX850 [Maxos Led Industry]

Maxos LED

Dimensional drawing



Photometric data



Polar Normal (separate) - 4MX8501 - 910629121726

