



Maxos LED Performer

4MX900 LED60S/840 PSD WB SI L1800

Maxos LED Performer, Trunking light panel, 37.3 W, L1800 mm, 6000 lm, 4000 K, DALI, Wide beam, Clear, Silver, IP40

Trunking light panel, L1800 mm, Aluminium, Silver, Power supply unit with DALI interface, 6000 lm, 37.3 W, 161 lm/W, 4000 K, (0.38, 0.38) SDCM <3.5, Wide beam, Clear, Polymethyl methacrylate, IP40 | Wire-protected, IK02 | 0.2 J standard, Safety class I, Connection unit 5-pole

Product data

General Information	
Lamp family code	LED60S [LED Module, system flux 6000 lm]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years
Light Technical	
Luminous Flux	6,000 lm
Saturated Red (R9)	<50
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	161 lm/W
Colour rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white

Optic type	Wide beam
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	Not applicable
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.192 ms
Power Consumption	37.3 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB (16 A type B)	29
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	20 %

Maxos LED Performer

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	1,800 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (height x width x depth)	82 x 87 x 1800 mm
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	2.900 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C

Remarks * – According to the Lighting Europe guidance paper 'Evaluating the performance of LED -based luminaires – January 2018'; statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median

useful life (B50) value also represents the B10 value.

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤4

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L90
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.

Product Data

Order product name	4MX900 LED60S/840 PSD WB SI L1800
Full product name	4MX900 LED60S/840 PSD WB SI L1800
Full EOC	403073266436899
Order code	910629136426
Material no. (12 NC)	910629136426
Numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732664368
Numerator – packs per outer box	2
EAN/UPC - Case	4030732262182
Product family code	4MX900 [Maxos LED Performer]

Maxos LED Performer

Dimensional drawing

