



Maxos LED Performer

4MX900 491 LED40S/840 PSU WB WH

Maxos LED Performer, Trunking light panel, 25.2 W, L1479 mm, 4000 lm, 4000 K, Wide beam, Clear, White, IP40

Trunking light panel, L1479 mm, Aluminium, White, Power supply unit (On/Off), 4000 lm, 25.2 W, 158 lm/W, 4000 K, (0.38, 0.38) SDCM <3.5, Wide beam, Clear, Polymethyl methacrylate, IP40 | Wire-protected, IK02 | 0.2 J standard, Safety class I, Connection unit 3-pole

Product data

General Information	
Lamp family code	LED40S [LED module, system flux 4000 lm]
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Service Tag	Yes
Lighting Technology	LED
Value ladder	Performance
Warranty period	5 years

Light Technical	
Luminous Flux	4,000 lm
Saturated Red (R9)	<50
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	158 lm/W
Colour rendering index (CRI)	>80
Number of light sources	1
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white

Optic type	Wide beam
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power Consumption	25.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB (16 A type B)	24
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Total harmonic distortion	20 %

Maxos LED Performer

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

Mechanical and Housing	
Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	1,479 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (height x width x depth)	82 x 87 x 1479 mm
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	2.500 kg

Approval and Application	
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* – According to the Lighting Europe guidance paper 'Evaluating the performance of LED - based luminaires – January 2018; statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤4


Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) L90 at median useful life* 50000 h	
Lumen maintenance (EN-IEC 62722-2-1) L80 at median useful life* 100000 h	

Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class C, the driver of this luminaire can be replaced by a service technician. Special care is required during disassembly and reassembly, and specific tools may be required. Parts and documentation are available for a period of time.
Embedded carbon (A1-A3)	54.7 kg CO _{2e}
Product non-virgin material ratio	7.26 %
Recyclable the content ratio of the finished product	45.9 %
GWP total B6 (kg CO _{2eq}) Declared Unit	Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO _{2eq} / kWh)
GWP total B6 (kg CO _{2eq}) Functional Unit	Please calculate using your local energy mix value: POWER DECLARED UNIT (kW) * 1000 (lm) / LUMEN OUTPUT DECLARED UNIT (lm) * 35000 (hrs) * ENERGY MIX (kg CO ₂ eq / kWh)


Product Data	
Order product name	4MX900 491 LED40S/840 PSU WB WH
Full product name	4MX900 491 LED40S/840 PSU WB WH
Full EOC	403073266492499
Order code	910629142026
Material no. (12 NC)	910629142026
Numerator – quantity per pack	1
EAN/UPC – Product/Case	4030732664924
Numerator – packs per outer box	2
EAN/UPC - Case	4030732262748
Product family code	4MX900 [Maxos LED Performer]

Maxos LED Performer

Dimensional drawing



Photometric data



Polar Normal (separate) - 4MX9001 - 910629142026

