

# DigiStreet

## BGP760 LED10-/740 I DM10 DGR 32-48

BGP760 | DigiStreet Micro, LED10 | LED Module 1000 lm, 740 neutral white, Safety class I, Distribution medium 10, Spigot for diameter 32 to 48 mm

Road & street light, Aluminum die cast, Dark gray, Spigot for diameter 32 to 48 mm, Power supply unit (On/Off), 900 lm, 6.8 W, 132 lm/W, 4000 K, (0.38. 0.38) SDCM <5, CRI70, Distribution medium 10, IP66 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class I, Surge protection level until 6 kV differential mode and 8 kV common mode, Screw connector

### Product data

General Information		Color rendering index (CRI)	
Lamp family code	LED10 [LED Module 1000 lm]	Color rendering index (CRI)	70
Light source replaceable	Yes	Number of light sources	1
Number of gear units	1 unit	Light source color	740 neutral white
Gear	EB [Electronic]	Luminaire light beam spread	157° - 33° x 55°
Driver included	Yes	Optic type outdoor	Distribution medium 10
Light source engine type	LED	Effective projected area	0.0578 m²
Service tag	Yes	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220-240 V
Value ladder	Specification	Line Frequency	50 to 60 Hz
Warranty period	5 years	Inrush current	15 A
Light Technical		Inrush time	0.295 ms
Upward light output ratio	0	Power Consumption	6.8 W
Luminous Flux	900 lm	Power Factor (Fraction)	0.95
Correlated Color Temperature (Nom)	4000 K	Connection	Screw connector
Luminous Efficacy (rated) (Nom)	132 lm/W	Cable	-

Number of products on MCB of 16 A type B	48
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 6 kV differential mode and 8 kV common mode

**Controls and Dimming**

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

**Mechanical and Housing**

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 32 to 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	695 mm
Overall width	236 mm
Overall height	103 mm
Dimensions (Height x Width x Depth)	103 x 236 x 695 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	Flat glass
Net Weight (Piece)	5.825 kg

**Approval and Application**

Glow-wire test	Temperature 650 °C, duration 5 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C

**Remarks** \* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. \* At extreme ambient temperatures the luminaire

	might automatically dim down to protect components
Ambient temperature range	-40 to +50 °C

**Initial Performance (IEC Compliant)**

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

**Over Time Performance (IEC Compliant)**

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L99
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L98

**Sustainability Data**

Sustainability rating	Signify Circle
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.

Embedded carbon (A1-A3)	127 kg CO <sub>2</sub> e
Product non-virgin material ratio	7.43 %
Recyclable content ratio of the finished product	53.7 %

**GWP total B6 (kg CO<sub>2</sub>eq) Declared Unit** Please calculate using your local energy mix value: Power Declared Unit (kW) \* Service life (hrs) Declared Unit \* Energy mix (kg CO<sub>2</sub>eq / kWh)

**GWP total B6 (kg CO<sub>2</sub>eq) Functional Unit** Please calculate using your local energy mix value: Power Declared Unit (kW) \* 1000 (lm) / lumen output (lm) Declared Unit \* 35000 (hrs) \* Energy mix (kg CO<sub>2</sub> eq / kWh)

**Non-virgin material ratio of the packaging** Cardboard > 80% recycled Plastic >35% recycled

**Packaging Recyclable content ratio** Cardboard recycling rate > 80% Plastic recycling rate > 40%

**Packaging Material** Cardboard Plastic


**Product Data**

Order product name	BGP760 LED10-/740 I DM10 DGR 32-48
Full product name	BGP760 LED10-/740 I DM10 DGR 32-48
Full product code	871869637679900
Order code	910925863554
Material Nr. (12NC)	910925863554


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696376799
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696376799

Product family code	BGP760 [DigiStreet Micro]
---------------------	---------------------------

Dimensional drawing



Photometric data



Polar Normal (separate) - BGP760I - 910925863554

