



Maxos fusion

LL500Z SMB BK

LL500Z | Maxos fusion Acc., Black

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information	
Service tag	Yes
Value ladder	Specification
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-
Mechanical and Housing	
Overall length	65 mm
Overall width	40 mm
Overall height	25 mm
Dimensions (Height x Width x Depth)	25 x 40 x 65 mm

Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Accessory color	Black
Net Weight (Piece)	0.030 kg

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

Sustainability Data	
Non-virgin material ratio of the packaging	Cardboard > 80% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80%

Maxos fusion

Packaging Material	Cardboard
Product Data	
Order product name	LL500Z SMB BK
Full product name	LL500Z SMB BK
Full product code	871869637450499
Order code	910925864220
Material Nr. (12NC)	910925864220

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696374504
Numerator - Packs per outer box	40
EAN/UPC - Case	8718696383384
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

