



Maxos fusion

LL500Z MB-SW WH

LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Product data

General Information		Material	
Service Tag	Yes	Material	Steel
Value ladder	Specification	Ingress protection code	-
Operating and Electrical		Mech. impact protection code	-
Input Voltage	- V	Accessory colour	White
Line Frequency	- Hz	Net Weight (Piece)	0.038 kg
Protection class IEC	-	Approval and Application	
Mechanical and Housing		CE mark	Yes
Overall length	65 mm	EU RoHS compliant	Yes
Overall width	40 mm	Product Data	
Overall height	50 mm	Order product name	LL500Z MB-SW WH
Dimensions (height x width x depth)	50 x 40 x 65 mm	Full product name	LL500Z MB-SW WH
		Full EOC	871869637451199

Maxos fusion

Order code	910925864221
Material no. (12 NC)	910925864221
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696374511
Numerator – packs per outer box	40

EAN/UPC - Case	8718696383391
Product family code	LL500Z [Maxos fusion Acc.]

Dimensional drawing

