

LL500Z PB WH

910925864227



LL500Z | Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

General Information

Service Tag	Yes
Value ladder	Specification


Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

Mechanical and Housing

Overall length	65 mm
Overall width	40 mm
Overall height	35 mm
Overall diameter	0 mm
Dimensions (height x width x depth)	35 x 40 x 65 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	-

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925864227_en_GB.txt	Download 

Accessory colour	White
Net Weight (Piece)	0.035 kg

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Product Data

Order product name	LL500Z PB WH
Full product name	LL500Z PB WH
Full EOC	871869637454299
Order code	910925864227
Material no. (12 NC)	910925864227
Numerator - quantity per pack	1
EAN/UPC — Product/Case	8718696374542
Numerator - packs per outer box	40
EAN/UPC - Case	8718696383452
Product family code	LL500Z [Maxos fusion Acc.]