

LL500Z MB-SW2 L5000 SI

910925864231



LL500Z | Maxos fusion Acc., Silver

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

General Information

Service Tag	Yes
Value ladder	Specification

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes

Operating and Electrical

Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-


Product Data

Order product name	LL500Z MB-SW2 L5000 SI
Full product name	LL500Z MB-SW2 L5000 SI
Full EOC	871869637458099
Order code	910925864231
Material no. (12 NC)	910925864231
Numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696374580
Numerator – packs per outer box	20
EAN/UPC - Case	8718696383490
Product family code	LL500Z [Maxos fusion Acc.]

Mechanical and Housing

Overall length	180 mm
Overall width	120 mm
Overall height	40 mm
Dimensions (height x width x depth)	40 x 120 x 180 mm
Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	Silver
Net Weight (Piece)	0.124 kg

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Tender text	Tender_Text_910925864231_en_GB.txt	Download 